



IOL

One Piece (Anterior Chamber)




OPAB-16

Overall Length..... 12.50 mm
 Optic Diameter..... 6.0 mm
 Haptic Vault..... 0.4 mm
 Optic Design..... Bi Convex
 Positioning Holes..... none
 Material..... PMMA CQ UV
 Haptic Material..... PMMA
 A Constant / A.C.D..... 114.9 / 2.93 mm
 Available Powers..... 10-30 d. in 0.5 d. steps




OPAB-130

Overall Length..... 13.00 mm
 Optic Diameter..... 6.0 mm
 Haptic Vault..... 0.4 mm
 Optic Design..... Bi Convex
 Positioning Holes..... none
 Material..... PMMA CQ UV
 Haptic Material..... PMMA
 A Constant / A.C.D..... 114.9 / 2.93 mm
 Available Powers..... 10-30 d. in 0.5 d. steps



OPAB-135

Overall Length..... 13.50 mm
 Optic Diameter..... 6.0 mm
 Haptic Vault..... 0.4 mm
 Optic Design..... Bi Convex
 Positioning Holes..... none
 Material..... PMMA CQ UV
 Haptic Material..... PMMA
 A Constant / A.C.D..... 114.9 / 2.93 mm
 Available Powers..... 10-30 d. in 0.5 d. steps



Hanita
Lenses

www.hanitalenses.com • email: marketing@hanitalenses.com

CE 0473

Hanita Lenses • Intraocular & Contact Lenses • Kibbutz Hanita 22885 Israel • Tel. 972 4 9950700 • Israel: 1 800 330 331 • Fax. 972 4 9950755
 European Authorized Rep. OBELIS S.A., 34, avenue de Tervuren, Bte 44, 1040 Brussels, Belgium.