

# DECLARATION OF CONFORMITY

of the  
**Vestfrost product Type: See Enclose No. 1.**

Made in Denmark by A/S Vestfrost  
 Falkevej 12, 6705 Esbjerg Ø, Denmark and Sp. Møllevej 100, 6705 Esbjerg Ø, Denmark  
 Telephone 45 79 14 25 25 Telephone 45 79 14 22 22

The undersigned declares that the equipment concerned complies with the below Directives and Standards

|                                                                                                 |                                                  |                                     |
|-------------------------------------------------------------------------------------------------|--------------------------------------------------|-------------------------------------|
| <b>Low Voltage Directive</b>                                                                    | 2014/35/EU<br>and subsequent modification        | <input checked="" type="checkbox"/> |
| <b>Electromagnetic Compatibility Directive</b>                                                  | 2014/30/EU<br>and subsequent modification        | <input checked="" type="checkbox"/> |
| <b>Machinery Directive</b>                                                                      | 2006/42/EU                                       | <input checked="" type="checkbox"/> |
| <b>RoHS Directive</b><br>Restriction of use of certain hazardous substances                     | 2011/65/EU                                       | <input checked="" type="checkbox"/> |
| <b>REACH Regulation</b><br>Registration, Evaluation, Authorisation and Restriction of Chemicals | 1907/2006/EC                                     | <input checked="" type="checkbox"/> |
| <b>WEEE Directive</b><br>waste electrical and electronic equipment (product design and marking) | 2012/19/EU                                       | <input checked="" type="checkbox"/> |
| <b>Eco design Directive</b><br>Eco design of professional refrigerated storage cabinets         | 2017/1369/EU<br>2015/1095                        | <input type="checkbox"/>            |
| <b>Labelling Regulation</b><br>Energy labelling of professional refrigerated storage cabinets   | 2017/1369/EU<br>2015/1094                        | <input type="checkbox"/>            |
| <b>Substances that Deplete the Ozone Layer</b><br>Restriction of use of CFC, HCFC and HFC       | Montreal Protocol<br>and subsequent modification | <input checked="" type="checkbox"/> |

The products listed have been manufactured according to the following Harmonized European Standards

|                                                                                                                                                                  |                                                              |                                     |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|-------------------------------------|
| <b>Safety of household electrical appliances</b><br>Part 1: General requirements                                                                                 | EN 60 335-1:2012+A11+A13<br>IEC 60335-1:2010+A1+A2           | <input checked="" type="checkbox"/> |
| <b>Safety of household and similar electrical appliances</b><br>Part 2: Particular requirements for refrigerating appliances, ice-cream appliances and icemakers | EN 60335-2-89:2010<br>IEC 60335-2-89:2010+A1:2012            | <input checked="" type="checkbox"/> |
| <b>Electromagnetic Fields</b>                                                                                                                                    | EN 62233:2008                                                | <input checked="" type="checkbox"/> |
| <b>Electromagnetic Compatibility, Immunity</b><br>Commercial and light Industrial environments                                                                   | EN 61000-6-1:2019<br>IEC 61000-6-1: 2016                     | <input checked="" type="checkbox"/> |
| <b>Electromagnetic Compatibility, Emission</b><br>Commercial and light Industrial environments                                                                   | EN 61000-6-3: 2007 + A1:2011<br>IEC 61000-6-3:2006 + A1:2010 | <input checked="" type="checkbox"/> |

**A/S VESTFROST**

2021.04.29

Jørgen Dyrholm

name

Esbjerg Denmark

**VESTFROST**  
 SOLUTIONS

A/S Vestfrost  
 Falkevej 12

DK-6705 Esbjerg Ø, Denmark  
 Tel.: +45 79 14 22 22 · Fax: +45 79 14 23 55

*Jørgen Dyrholm*  
 signature

Esbjerg Denmark

**A/S Vestfrost**

Falkevej 12

DK-6705 Esbjerg Ø

Tel. +45 79 14 22 22

Fax +45 79 14 22 55

www.vestfrostsolutions.com

CVR. 37101117

Enclosure No. 1.

Declaration of Conformity

Date 29-04-2021

| <u>Identification</u> | <u>Type or product No.</u> | <u>Trade name.</u> | <u>Type</u> |
|-----------------------|----------------------------|--------------------|-------------|
| VESTFROST             | VT 78 -86°C                | NORDIC LAB         | ULT C75     |
| VESTFROST             | VT 208 -86°C               | NORDIC LAB         | ULT C200    |
| VESTFROST             | VT 308 -86°C               | NORDIC LAB         | ULT C300    |
| VESTFROST             | VT 408 -86°C               | NORDIC LAB         | ULT C400    |
| VESTFROST             | VT 146 -45°C               | NORDIC LAB         | LT C150     |
| VESTFROST             | VT 206 -45°C               | NORDIC LAB         | LT C200     |
| VESTFROST             | VT 306 -45°C               | NORDIC LAB         | LT C300     |
| VESTFROST             | VT 406 -45°C               | NORDIC LAB         | LT C400     |
| VESTFROST             | VT 546 -45°C               | NORDIC LAB         | LT C500     |
| VESTFROST             | VT 75 -60°C                | NORDIC LAB         | XLT C75     |
| VESTFROST             | VT 147 -60°C               | NORDIC LAB         | XLT C150    |
| VESTFROST             | VT 207 -60°C               | NORDIC LAB         | XLT C200    |
| VESTFROST             | VT 307 -60°C               | NORDIC LAB         | XLT C300    |
| VESTFROST             | VT 407 -60°C               | NORDIC LAB         | XLT C400    |
| VESTFROST             | VT 547 -60°C               | NORDIC LAB         | XLT C500    |
| VESTFROST             | VT S 098                   | NORDIC LAB         | ULT U100    |
| VESTFROST             | VT S 252                   | NORDIC LAB         | MLT U250    |
| VESTFROST             | VT S 254                   | NORDIC LAB         | LT U250     |
| VESTFROST             | VT S 256                   | NORDIC LAB         | XLT U250    |
| VESTFROST             | VT S 258 Dual              | NORDIC LAB         | ULT U250    |
| VESTFROST             | VT 74 -25°C                | NORDIC LAB         | MLT C75     |
| VESTFROST             | ULTF 37                    | NORDIC LAB         | ULT U35     |