




simpass END035

.035" OTW PTA BALLOON DILATATION CATHETER

LOW PROFILE TIP

Weld-formed tip for challenging lesions

LARGE INFLATION LUMEN

Enables fast inflation/deflation

LOW PROFILE REWRAP

Balloon folding geometry minimizes profile & allows smooth rewrap

CATHETER COATING

Hydrophilic coated OTW shaft for improved crossability



Nominal Pressure	8 atm
Rated Burst Pressure	3 mm - 8 mm : 16 atm 9 mm - 12 mm : 14 atm
Marker Bands	Swaged 1 mm Platinum Iridium Markers (Distal & Proximal)
Guidewire Compatibility	0.035" GW compatible wire tracking lumen (OTW)
Tip Entry Profile	0.044"
Sheath Compatibility	3 mm - 6 mm : 5 F 7 mm - 8 mm : 6 F 9 mm - 12 mm : 7 F
Balloon Fold	3 mm - 6 mm : 3 Fold 7 mm - 12 mm : 6 Fold
Catheter Coating	Hydrophilic Coating

50cm Catheter Product Code	80cm Catheter Product Code	130cm Catheter Product Code	Balloon Diameter (mm)	Balloon Length (mm)	Nominal Pressure (atm)	Rated Burst Pressure (atm)	Recommended Introducer Sheath (F)
SE30020-50	SE30020-80	SE30020-130	3.0	20	8	16	5
SE30030-50	SE30030-80	SE30030-130	3.0	30	8	16	5
SE30040-50	SE30040-80	SE30040-130	3.0	40	8	16	5
SE30050-50	SE30050-80	SE30050-130	3.0	50	8	16	5
SE30060-50	SE30060-80	SE30060-130	3.0	60	8	16	5
SE30080-50	SE30080-80	SE30080-130	3.0	80	8	16	5
SE300100-50	SE300100-80	SE300100-130	3.0	100	8	16	5
SE300150-50	SE300150-80	SE300150-130	3.0	150	8	16	5
SE300200-50	SE300200-80	SE300200-130	3.0	200	8	16	5
SE300220-50	SE300220-80	SE300220-130	3.0	220	8	16	5
SE40020-50	SE40020-80	SE40020-130	4.0	20	8	16	5
SE40030-50	SE40030-80	SE40030-130	4.0	30	8	16	5
SE40040-50	SE40040-80	SE40040-130	4.0	40	8	16	5
SE40050-50	SE40050-80	SE40050-130	4.0	50	8	16	5
SE40060-50	SE40060-80	SE40060-130	4.0	60	8	16	5
SE40080-50	SE40080-80	SE40080-130	4.0	80	8	16	5
SE400100-50	SE400100-80	SE400100-130	4.0	100	8	16	5
SE400150-50	SE400150-80	SE400150-130	4.0	150	8	16	5
SE400200-50	SE400200-80	SE400150-130	4.0	200	8	16	5
SE400220-50	SE400220-80	SE400220-130	4.0	220	8	16	5
SE50020-50	SE50020-80	SE50020-130	5.0	20	8	16	5
SE50040-50	SE50040-80	SE50040-130	5.0	40	8	16	5
SE50060-50	SE50060-80	SE50060-130	5.0	60	8	16	5
SE50080-50	SE50080-80	SE50080-130	5.0	80	8	16	5
SE500100-50	SE500100-80	SE500100-130	5.0	100	8	16	5
SE500150-50	SE500150-80	SE500150-130	5.0	150	8	16	5
SE500220-50	SE500220-80	SE500220-130	5.0	220	8	16	5
SE60020-50	SE60020-80	SE60020-130	6.0	20	8	16	5
SE60040-50	SE60040-80	SE60040-130	6.0	40	8	16	5
SE60060-50	SE60060-80	SE60060-130	6.0	60	8	16	5
SE60080-50	SE60080-80	SE60080-130	6.0	80	8	16	5
SE600100-50	SE600100-80	SE600100-130	6.0	100	8	16	5
SE70040-50	SE70040-80	SE70040-130	7.0	40	8	16	6
SE70060-50	SE70060-80	SE70060-130	7.0	60	8	16	6
SE70080-50	SE70080-80	SE70080-130	7.0	80	8	16	6
SE700100-50	SE700100-80	SE700100-130	7.0	100	8	16	6
SE80040-50	SE80040-80	SE80040-130	8.0	40	8	16	6
SE80060-50	SE80060-80	SE80060-130	8.0	60	8	16	6
SE80080-50	SE80080-80	SE80080-130	8.0	80	8	16	6
SE800100-50	SE800100-80	SE800100-130	8.0	100	8	16	6
SE90040-50	SE90040-80	SE90040-130	9.0	40	8	14	7
SE90060-50	SE90060-80	SE90060-130	9.0	60	8	14	7
SE10040-50	SE10040-80	SE10040-130	10.0	40	8	14	7
SE10060-50	SE10060-80	SE10060-130	10.0	60	8	14	7
SE12040-50	SE12040-80	SE12040-130	12.0	40	8	14	7
SE12060-50	SE12060-80	SE12060-130	12.0	60	8	14	7

Please consult sales representative for different size requests.

REV05-270125-B