



One Piece (Anterior Chamber)




OPAB-16

Overall Length..... 12.50 mm
 Optic Diameter..... 6.0 mm
 Haptic Vault..... 0.4 mm
 Optic Design..... Bi Convex
 Positioning Holes..... none
 Material..... PMMA CQ UV
 Haptic Material..... PMMA
 A Constant / A.C.D..... 114.9 / 2.93 mm
 Available Powers..... 10-30 d. in 0.5 d. steps



OPAB-130

Overall Length..... 13.00 mm
 Optic Diameter..... 6.0 mm
 Haptic Vault..... 0.4 mm
 Optic Design..... Bi Convex
 Positioning Holes..... none
 Material..... PMMA CQ UV
 Haptic Material..... PMMA
 A Constant / A.C.D..... 114.9 / 2.93 mm
 Available Powers..... 10-30 d. in 0.5 d. steps



OPAB-135

Overall Length..... 13.50 mm
 Optic Diameter..... 6.0 mm
 Haptic Vault..... 0.4 mm
 Optic Design..... Bi Convex
 Positioning Holes..... none
 Material..... PMMA CQ UV
 Haptic Material..... PMMA
 A Constant / A.C.D..... 114.9 / 2.93 mm
 Available Powers..... 10-30 d. in 0.5 d. steps

