



Binocular brightfield microscope, 1000x, N-PLAN objectives

| Observation Method - Transmitted Light | Brightfield | Yes |
|---|---------------------------------------|-------------------------------------|
| | Darkfield | As optional |
| | Simple polarized light | As optional |
| | | |
| Main Body | Туре | Upright |
| | Construction material | Aluminum die-cast |
| | Trasportation handle | Yes |
| | | |
| Head | Туре | Binocular (Siedentopf) |
| | Inclination | 30° |
| | 360° rotating | Yes |
| | Interpupillary distance (mm) | 48-75 |
| | Dioptric adjustement | On left tube |
| | Fixing screw for eyepieces | Yes |
| | Tube inner diameter (mm) | 23 |
| | | |
| Eyepieces | Field number (mm) | 20 |
| | Magnification | 10x |
| | Pointer | As optional |
| | Micrometric scale | As optional |
| | Diameter of micrometer glass (mm) | 21 |
| | High eyepoint (for glass wearers) | Yes |
| | Rubber cup | Yes |
| | | |
| Nosepiece | Positions | Quadruple |
| | Reversed | Yes |
| | Bi-directional | Yes |
| | Rotation on ball bearings | Yes |
| | Objective thread | RMS |
| | | |
| Objectives | Optical system | 160 |
| | Anti-fungus treatment | Yes |
| | Parfocal distance (mm) | 45 |
| | Standard magnifications | 40x-1000x |
| | Туре | N-PLAN |
| | Objectives included | 4x/0.10, W.D. 15.2 mm |
| | , | 10x/0.25, W.D. 5.5 mm |
| | | 40x/0.65, W.D. 0.45 mm |
| | | 100x/1.25 (Oil/Water), W.D. 0.13 mm |
| | | |
| Stage | Туре | Double layer |
| | Dimensions (mm) | 150x139 |
| | Moving mechanism | Rackless |
| | Moving meenanism Moving range (mm) | 75x33 |
| | Material | Anti-scratch painting |
| | Specimen holder | Yes |
| | Slide number | 1 |
| | X-Y Vernier scale | Yes |
| | | |
| | Vernier scale accuracy (mm) | 0.1 |

www.optikamicroscopes.com - info@optikamicroscopes.com

| Condenser - Single | Туре | Abbe |
|------------------------|--|---|
| Position | Removable | Yes |
| | Numerical aperture (N.A.) | 1.25 |
| | Magnification scale for simplified positioning | Yes |
| | Diaphragms | Iris |
| | Centrable | Yes |
| | Focusable | By rack and pinion |
| | | |
| Focusing System | Туре | Coaxial coarse & fine |
| | Coarse total travel (mm) | 18 |
| | Fine total travel (per single rotation) (mm) | 0.4 |
| | Fine graduations | 100 |
| | Fine resolution (µm) | 4 |
| | Upper stop to prevent contact | Yes |
| | Adjustable tension | Yes |
| | | |
| Transmitted | Kohler illumination | Fixed |
| Illumination | Туре | X-LED |
| | X-LED type | X-LED3 |
| | Light source power (W) | 3.6 |
| | Brightness control | Manual |
| | Lifetime (hours) | > 65,000 |
| | Temperature (K) | 6,300 |
| | Max. required power (W) | 6 |
| | | |
| Power Supply for | Туре | External |
| Transmitted | Microscope connector | Jack, 2.1 mm |
| Illumination | Power plug type | Multi-plug (EU, UK, US) |
| | Input voltage | 100/240 Vac, 50/60 Hz |
| | Output voltage | 6 Vdc 2.5 A |
| | | |
| Accessories Included | Dust cover | Yes |
| | Immersion oil (10ml) | Yes |
| | Tension adjustment tool | Yes |
| | User Manual | Digital version (downloadable) |
| | | |
| Additional Information | | Mirror for transmitted light (as optional). |
| | | External rechargeable battery pack (as optional). |
| Product Dimensions | Height (mm) | 370 |
| | Width (mm) | 235 |
| | | 320 |
| | Depth (mm) | 320 |
| Product Weight | (kg) | 6.5 |
| Fibuuct weight | (kg) | 6.5 |