XG1.U Steam Sterilizer

Product introduction

It can be widely used in department of stomatology and ophthalmology, operating room and other medical institutions. It is suitable for all wrapped or unwrapped solid instruments, A-class cavity instrument (dental hand-pieces and endoscopes), implantable instruments, dressing fabric and rubber tubes, etc.

Product features

- Equipped with professional and systematized sterilizing programs of fabric, instrument, rubber, liquid, cavity, testing and auxiliary programs of BD, PCD and leakage.
- Temperature, pressure, time, running status, failure warning liquid-crystal display.
- Intelligentized drying system to guarantee the residual humidity of instrument and dressing no more than 0.2% and 1% respectively.
- Build-in efficient steam generator, microcomputer temperature control, time and energy saving.
- Equipped with printer to print date, time and process parameters.
- Over-heat auto protection device, dual door safety lock device, overpressure relief valve, short-circuit protection, and overpressure protection.
- Perfect four-level authority management system to avoid misoperation.



Design pressure: -0.1/0.25MPa

Accuracy of temperature display: 0.1 C

Vacuum limit: -0.080MPa Chamber material: 304 stainless steel

Sterilization working temperature: 115~138 C

Configuration Selections Table

XG1.U Basic configuration

No.	Order code	Volume (L)	Chamber size (φ×L) mm	Overall size (L×W×H) mm	Net weight (kg)	Input power (kVA)
1	XG1.UCD-100D	100	400×850	1250×730×1660	260	10
2	XG1.UCD-100S	100	400×780	1264×730×1660	300	10
3	XG1.UCD-135D	135	500×710	1110×750×1742	400	11.5
4	XG1,UCD-135S	135	500×620	1140×750×1742	450	11.5
5	XG1.UCD-185D	185	500×950	1350×750×1742	460	11.5
6	XG1.UCD-185S	185	500×860	1365×750×1742	500	11.5
7	XG1.UCD-300D	300	632×1000	1415×890×1780	750	18
8	XG1.UCD-300S	300	632×890	1438×890×1780	800	18

 Number of Door(s) ☐ D-Single door ☐ S-Double door

 Material of Chamber + Jacket ☐ SUS304+SUS304 ☆ ☐ SUS316L+SUS316L

o Material of Built-in steam generator ☐ SUS304 ☆ ☐ SUS316L

 Loading mode ☐ Shelf loading

 Voltage ☐ 380V, 3-Phases☆ ☐ 220V, 3-Phases 240V, 3-Phases ☐ 415V, 3-Phases

☐ 400V, 3-Phases

 Frequency □ 50Hz ☆ □ 60Hz

 Standard accessories ☐ Loading shelves×2

XG1.C Steam Sterilizer

Product introduction

It is applicable for the sterilization of unpacked solid instrument in department of stomatology, ophthalmology, operation room and CSSD.

Product features

- Touch screen display of temperature, pressure, time, running status and
- Equipped with professional and systematized sterilizing programs of fabric, instrument, rubber and liquid.
- The positive pressure air-discharging system will effectively discharge the cold air from chamber to improve steam saturability.
- O Build-in efficient steam generator, microcomputer temperature control, time and energy saving.
- Equipped with post-drying function which makes the residual humidity of sterilized articles less than 3%.
- Equipped with printer to print date, time and process parameters.
- Over-heat auto protection device, dual door safety lock device, overpressure relief valve, short-circuit protection and overpressure protection.
- Perfect four-level authority management system to avoid misoperation.



Technical parameters

Design pressure: 0 / 0.25MPa Chamber material: 304 stainless steel Maximum working pressure: 0.23MPa Accuracy of temperature display: 0.1 C Sterilization working temperature: 115~138 C Accuracy of pressure display: 1Kpa

Configuration Selections Table

XG1.C Basic configuration

No.	Order code	Volume (L)	Chamber size (φ×L) mm	Overall size (L×W×H)mm	Net weight (kg)	Input power (kVA)
1	XG1.CD-100D	100	400×850	1250×730×1660	260	10
2	XG1.CD-100S	100	400×780	1264×730×1660	300	10
3	XG1.CD-135D	135	500×710	1110×750×1742	400	11
4	XG1.CD-135S	135	500×620	1140×750×1742	450	11
5	XG1.CD-185D	185	500×950	1350×750×1742	460	11
6	XG1.CD-185S	185	500×860	1365×750×1742	500	11
7	XG1.CD-300D	300	632×1000	1415×890×1780	750	17
8	XG1.CD-300S	300	632×890	1438×890×1780	800	17

 Material of Built-in 	o Voltage		
steam generator	☐ 380V, 3-Phases☆	☐ 220V, 3-Phases	
☐ SUS304 ☆	☐ 240V, 3-Phases	☐ 400V, 3-Phases	
□ SUS316L	☐ 415V, 3-Phases		
 Loading mode 	 Frequency 	 Standard accessories 	
☐ Shelf loading	□ 50Hz ☆ □ 60Hz	☐ Loading shelves×2	
	steam generator □ SUS304 ☆ □ SUS316L • Loading mode	Steam generator	

14 15