





normal vessels / standard cases	tortuous vessels / complex cases
 ASAHI CHIKAI 10 ASAHI CHIKAI 008	 ASAHI CHIKAI black ASAHI CHIKAI black 18
 tiny vessels / precision cases	 large vessels / high support cases

Specification & ordering information						
Product	Catalog No.	O.D.	Coating	Usable length	Coil length	Tip shape
ASAHI CHIKAI 008	WAN-CH-008-200	0.20 (0.26mm) (0.008") (0.008")	Hydrophilic coating (SIP-COAT™) 180mm	200mm	8mm	Straight
	WAN-CH-16-200	0.26mm (0.010mm)	Hydrophilic coating (SIP-COAT™) 170mm	200mm	9.5mm	Straight
	WAN-CH-16-000	0.26mm (0.010mm)	Hydrophilic coating (SIP-COAT™) 170mm	300mm	9.5mm	Straight
ASAHI CHIKAI	WAN-CH-300	0.26mm (0.014mm)	Hydrophilic coating (SIP-COAT™) 170mm	200mm	30mm	Straight
	WAN-CH-300-HC	0.26mm (0.014mm)	Hydrophilic coating (SIP-COAT™) 170mm	200mm	30mm	Round curve
	WAN-CH-300	0.26mm (0.014mm)	Hydrophilic coating (SIP-COAT™) 170mm	300mm	30mm	Straight
ASAHI CHIKAI black	WAN-CH-300-HC	0.26mm (0.014mm)	Hydrophilic coating (SIP-COAT™) 170mm	300mm	30mm	Round curve
	WAN-CH-300-HS	0.26mm (0.014mm)	Polymer jacket / Hydrophilic coating (SIP-COAT™) 170mm	200mm	30mm	Round curve
	WAN-CH-300-SA	0.26mm (0.014mm)	Polymer jacket / Hydrophilic coating (SIP-COAT™) 170mm	200mm	30mm	Angled 90°
ASAHI CHIKAI black 18	WAN-CH-18-200-BS	0.45 (0.41mm) (0.018") (0.016mm)	Hydrophilic coating (SIP-COAT™) 170mm	200mm	34mm	Round curve



Not all names and figures are available in all countries. Please check carefully with your sales representative.
Control with S-P-COAT™ system.

ASAHI CHIKAI and ACT ONE are trademarks or registered trademarks of ASAHI INTECC CO., LTD. in Japan and other countries.

Manufactured by:

ASAHI INTECC
ASAHI INTECC CO., LTD.
9-1100 Aikawa-cho, Saito, Aichi 486-0271 Japan
Contact phone number: +81-561-46-0101
<http://www.asahi-intecc.com>

Distributed by:

ASAHI INTECC
Your dreams. Woven together.

ASAHI CHIKAI Family


Neurovascular Guidewire

ASAHI CHIKAI Family

Neurovascular GuideWire

Providing good torque response, support and durability for neuro interventional procedures

ASAHI CHIKAI family of guide wires has been originally developed based on Asahi Intecc's unique set of technologies which accomplished great success in the field of cardiovascular interventions.



Technologies with Dual-coil design using ACT ONE

Employs the ASahi brand rope coil which provides torqueability, flexibility and resiliency. ASahi INTECC CO., LTD's unique technologies in wire drawing, wire forming, torque transmission and coating are utilized to create highly responsive guide wires featuring ASahi's ACT ONE dual-coil design.



Key features

- Precise torque response**
 - ACT ONE provides exceptional torque response in tortuous anatomy.
- Durable tip-shape retention**
 - Incorporating with ACT ONE, re-shapable pre-shaped round curve and 90 degree angle enhance tip shape memory and durability.



Round curve
#Available for CHIKAI
CHIKAI black and CHIKAI blue is

Angled 90°
#Available for CHIKAI black

ASAHI CHIKAI

Neurovascular GuideWire

ASAHI CHIKAI ASahi CHIKAI T0 and ASahi CHIKAI 008 are designed for an optimal balance between tip flexibility and microcatheter support




ASAHI CHIKAI 008 (200cm)

— Soft flexible tip & distal body

0.26mm (0.010")
0.008" (0.008")

- Tip radiopacity 8 cm
- SLIP-COATTM hydrophilic coating 180 cm

Distal anatomy / small-sized vessels
Compatible with microcatheters with small inner lumen



ASAHI CHIKAI T0 (200cm, 300cm)

— Balanced tip and higher body support

0.26mm (0.010")

- Tip radiopacity 8 cm
- SLIP-COATTM hydrophilic coating 170 cm

Mild to distal anatomy / larger-sized vessels
Compatible with microcatheters with relatively larger inner lumen



ASAHI CHIKAI (200cm, 300cm)

— 0.36mm (0.014") workhorse guide wire

0.36mm (0.014")

- Tip radiopacity 8 cm
- SLIP-COATTM hydrophilic coating 170 cm

Well-balanced workhorse wire



ASAHI CHIKAI black

Neurovascular GuideWire

Providing excellent support and less friction due to polymer jacket and hydrophilic coating for smooth delivery of microcatheter



ASAHI CHIKAI black (200cm)

— 0.36mm (0.014") guide wire with enhanced lubricity

0.36mm (0.014")

- Tip radiopacity 8 cm
- Polymer jacket length 150 cm
- SLIP-COATTM hydrophilic coating 170 cm

Complex cases and targeting distal anatomy
Ease distal aspiration catheter placement



ASAHI CHIKAI black 18 (200cm)

— Specialty guide wire

0.45mm (0.018")
0.41mm (0.016")
0.36mm (0.014")

- Tip radiopacity 8 cm
- Polymer jacket length 150 cm
- SLIP-COATTM hydrophilic coating 170 cm

Enough support to deliver large ID microcatheter
Reverse tapered shaft design to avoid ledge effect
Easy for retriever delivery and aspiration catheter placement

