

PE150AF CERMAX[®] XENON SHORT-ARC LAMPS



Cermax[®] Xenon short-arc lamps from Excelitas Technologies are ideal for applications that require a high degree of illumination control.

The Cermax[®] Xenon short-arc lamp from Excelitas Technologies is an innovative lamp design in the specialty lighting industry. Cermax[®] Xenon lamps were first introduced in the early 1980s and are now used in diagnostic and surgical endoscopes in most major hospitals worldwide, in high-brightness projection display systems, and for a wide variety of other high-performance applications.

The Cermax[®] Xenon lamp, Model PE150AF, has an integrated parabolic reflector, enabling high-intensity, focused light output. Due to the Xenon lamp's broad color spectrum, the lamp is filtered to emit ultraviolet, visible, or infrared light, depending upon application and usage. With their internal reflector and rugged ceramic body construction, Cermax[®] Xenon lamps are the safest and most compact alternative to conventional quartz xenon lamps. Cermax[®] lamps are ideal for applications that require a high degree of illumination control.

Current-regulated or power-regulated power supplies with output ripples of less than 5% are recommended. Single-shot ignition pulses are advised because radio frequency starters may damage the lamp's internal reflector.

In addition to lamps, Excelitas Technologies manufactures Cermax[®] Xenon short-arc lamp power supplies, lamp holders, OEM lighting systems, and fiber optic light sources.



Key Features

- High-intensity illumination—1350 Lumens
- Compact size
- Power range of 100-150 Watts
- 1000 hours lamp lifetime
- Broad spectral range with 5900° Kelvin color temperature

Applications

- Medical fiber optic illuminators
- Industrial fiber optic illuminators
- Machine vision
- Infrared and visible spotlights/beacons
- Spectroscopy
- Microscopy
- UV Curing
- Video projection



www.excelitas.com PE150AF 03/2012 page 1 of 4

PE150AF CERMAX[®] XENON SHORT-ARC LAMP

PE150AF

| Operational Specifications | | | | |
|----------------------------|------------------------------------|--------------------|--|--|
| Description | Nominal | Range | | |
| Power | 150 Watts | 100-150 Watts | | |
| Current | 11 amps (DC) | 10-14 amps (DC) | | |
| Operating Voltage | 11.7 Volts (DC) | 10-13.6 Volts (DC) | | |
| Ignition Voltage | 23 kilovolts (recommended minimum) | | | |
| Temperature | 120° C (Maximum) | | | |
| Lifetime* | 1000 hours typical | | | |

* End of life is defined as 50% of initial output

| Initial Output at Nominal Power | | |
|---------------------------------|--------------|--|
| F= UV Filtered Output | | |
| Description | PE150AF | |
| Radiant Output* | 16 Watts | |
| UV Output* | 0.9 Watts | |
| IR Output* | 8 Watts | |
| Visible Output* | 1350 Lumens | |
| Color Temperature | 5900° Kelvin | |
| Peak Instabilities | 4% | |

* These values indicate total output in all directions. Wavelengths = UV<390 nm, IR>770 nm, Visible: 390 nm-770 nm

| Physical Specifications | | |
|-------------------------|----------------------|--|
| Description | Specification | |
| Arc Gap | 0.038 inch (0.96 mm) | |
| Weight | 100 grams | |
| Window Diameter | 0.77 inch (19.6 mm) | |

PE150AF CERMAX[®] XENON SHORT-ARC LAMP

PE150AF

| Focused Output with a F/1.0 Lens | | | |
|----------------------------------|----------------|---------------|--|
| Description | Visible Output | Total Output* | |
| 3 mm aperture | 700 Lumens | 5.5 Watts | |
| 6 mm aperture | 900 Lumens | 8.0 Watts | |

* Nominal values at 150 watts after 2 hour burn-in.

NOTES:


1. Lamp must not be operated with window facing upwards within 45° of vertical.

2. Seal temperature must not exceed 120° C.

3. Current/power regulated power supplies and Excelitas lamp housing units are recommended.

4. Lamp must be operated within recommended current and power range. Over powering may lead to arc instability, hard starting and premature aging.


6. Cermax[®] Xenon lamps are much safer lamps to use than their quartz xenon arc lamp equivalents. However, caution must be practiced when operating the lamps because they are under high pressure, require high voltage, reach temperatures up to 200° C, and their IR and UV radiation can cause skin burns and eye damage. Please read hazard sheet included with each lamp shipment.



Mechanical Dimensions

PE150AF CERMAX[®] XENON SHORT-ARC LAMP

Spectral Output



About Excelitas Technologies

Excelitas Technologies is a global technology leader focused on delivering innovative, customized solutions to meet the lighting, detection and other high-performance technology needs of OEM customers.

From medical lighting to analytical instrumentation, clinical diagnostics, industrial, safety and security and aerospace and defense applications, Excelitas Technologies is committed to enabling our customers' success in their specialty end-markets. Excelitas Technologies has approximately 3,000 employees in North America, Europe and Asia, serving customers across the world.

Excelitas Technologies Illumination, Inc.

44370 Christy Street Fremont, California 94538-3180 USA Telephone: (+1) 510.979.6500 Toll-free: (+1) 800.775.6786 Fax: (+1) 510.687.1140 shortarcxenon.na@excelitas.com

Excelitas Technologies Singapore, Private Limited

47 Ayer Rajah Crescent #06-12 Singapore 139947 Telephone: (+65) 6775 2022 (Main Line) Telephone: (+65) 6770 4366 (Customer Service Hotline) Fax: (+65) 6778 1752 shortarcxenon.asia@excelitas.com

Excelitas Technologies GmbH & Co. KG Wenzel-Jaksch-Str. 31 D-65199 Wiesbaden Germany Telephone: (+49) 611 492 430 Fax: (+49) 611 492 165 shortarcxenon.europe@excelitas.com

Japan

Excelitas Technologies East Tower 4th Floor, Otemachi First Square 1-5-1 Otemachi, Chiyoda-ku, Tokyo 100-0004 Telephone: (+81) 3-5219-1228 Fax: (+81) 3-5219-120 shortarcxenon.asia@excelitas.com

For a complete listing of our global offices, visit www.excelitas.com/locations

© 2012 Excelitas Technologies Corp. All rights reserved. The Excelitas logo and design are registered trademarks of Excelitas Technologies Corp. All other trademarks not owned by Excelitas Technologies or its subsidiaries that are depicted herein are the property of their respective owners. Excelitas reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

