



Mobile X-Ray Barrier

- Lead Equivalency of Body : 2.0 mm Pb (according to IEC 61331-1:2014)
- Size : 195 cm (h) x 95 cm (w) (dimensions are customizable)
- Frame Material : Aluminum
- Lead Glass Size : 20x20 cm (dimensions are customizable)
- Lead Equivalency of Glass : 2.0 mm Pb @150 kV
- Description : 4 heavy duty wheels, two with locking brakes.

Note: When cleaning, please avoid using acidic or alkaline substances on glass section, and do not allow liquids to dry on the glass as this is likely to cause permanent staining. Always ensure that the glass is dried after any form of wetting.

The lead equivalent thicknesses determined during tests are in accordance with the values specified by the manufacturer. Measurements of lead equivalent were made according to the IEC 61331-1:2014 Protective devices against diagnostic medical X-radiation - Part 1: Determination of attenuation properties of materials.