



*Trinocular stereozoom microscope,
7x...45x, fixed arm, transmitted & incident
light*

Observation Method - Transmitted Light	Brightfield	Yes
Observation Method - Incident Light	Brightfield	Yes
Head	Type	Trinocular
	Construction material	Aluminum & Plastic molds / Aluminum gears
	Split ratio	50/50
	Inclination	45°
	360° rotating	Yes
	Interpupillary distance (mm)	51-75
	Dioptric adjustment	On both tubes
	Fixing screw for eyepieces	Yes
	Head holder internal diameter (mm)	76
	Tube inner diameter (mm)	30
Eyepieces	Field number (mm)	21
	Magnification	10x
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	24
	High eyepoint (for glass wearers)	Yes
	Rubber cup	Yes
Objective	Optical system	Greenough
	Anti-fungus treatment	Yes
	Objective Type	Achromatic
	Zoom type	Parfocal achromatic
	Working distance (mm)	100
	Standard magnifications	7x-45x
	Zoom ratio	6.43
Focusing System	Type	Coarse
	Coarse total travel (mm)	55
	Adjustable tension	Yes
	Head holder internal diameter (mm)	76
Stand	Type	Fixed arm
	Handle	Yes
Stage	White diffusion plate for transmitted ill.	Yes, diameter 60 mm
	Black/white contrast plate for incident ill.	Yes, diameter 60 mm
	Specimen clips	Yes
Transmitted Illumination	Type	LED
	Light source power (W)	3
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	5

Incident Illumination	Type	LED
	Light source power (W)	3
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	5
Power Supply for Illumination	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	6 Vdc 2.5 A
Accessories Included	Dust cover	Yes
	User Manual	Digital version (downloadable)
Additional Information	Maximum sample height (mm):	80
Product Dimensions	Total height (mm)	355
	Head height (mm)	225
	Head width (mm)	140
	Head depth (mm)	160
	Base height (mm)	44
	Base width (mm)	200
	Base depth (mm)	280
Product Weight	(kg)	3.6