



Anesthesiology and others
Product Catalog

SHUNMEI AND ITS SUBSIDIARIES

A.6 2022-05

 SHUNMEI MEDICAL CO.,LTD

Add: No.8 jinlong 1st street, Baolong Industrial Zone,
Longgang District, Shenzhen, China.
Branch Office: Yifa Industrial Zone, Dushi Village,
Pingtan Town, Huiyang District, Huizhou, China.
Mobile/Whatsapp: 86-183-4436 9007 86-183-4435 9973
E-mail: nora@shunmed.com nora1@shunmed.com
Website: www.shunmed.com

SHUNMEI SP. Z O.O.

SHUNMEİ MEDİKAL VE TIBBİ CİHAZLAR
TİCARET ANONİM ŞİRKETİ

Love in Shunmei Based on quality 

Shunmei[®]
顺美医疗



Company Profile

Shunmei Medical Co.,LTD was founded in 2009 and is headquartered in Shenzhen. We are committed to research and development, production and global sales of medical consumables related to Vascular intervention and Anesthesiology.

Our production sites are located in Huizhou city, Guangdong Province and Hunan Province. Huizhou production site covers an area of 20,300 square meters. Hunan production site covers an area of 33,300 square meters.

Our company has set up 3 overseas wholly-owned subsidiaries.

Mission :

Bring patient back to health.

Vision :

Become a world-class research & development and manufacturing enterprise of medical interventional products.




Catalogue

Central Venous Catheter Kit	01
Nitinol Guide Wire	04
Hemodialysis Catheter Kit	05
Zebra Guidewire	08
Disposable Pressure Transducer	09
Angiographic Syringe	11

Shun Monitor

Central Venous Catheter Kit



PRODUCT FEATURES :

- Excellent soft-tip to significantly reduce risk of vasular trauma.
- Medical grade material:catheter automatically softens under the temperature of 37°
- With radiopaque materials,ensure correct placement of the catheter tip.
- Length can be customized.

STANDARD KIT :

- Catheter
- Dilator
- Introducer needle(straight or Y type)
- Nitinol guide wire
- Syringe(or blue guiding syringe)
- Scalpel
- Injection cap
- Catheter clamp



Code	Lumen type	Size	Length (cm)	Distal	Middle	Proximal
609120	Single lumen	14G	14	120(108-138)	-	-
609101	Single lumen	14G	15	120(108-138)	-	-
609114	Single lumen	14G	16	120(108-138)	-	-
609102	Single lumen	14G	20	120(108-138)	-	-
609103	Single lumen	14G	30	120(108-138)	-	-
609104	Single lumen	16G	15	60(54-69)	-	-
609115	Single lumen	16G	16	60(54-69)	-	-
609105	Single lumen	16G	20	60(54-69)	-	-
609106	Single lumen	16G	30	60(54-69)	-	-
609110	Single lumen	18G	12	25(21-29)	-	-
609107	Single lumen	18G	13	25(21-29)	-	-
609108	Single lumen	18G	15	25(21-29)	-	-
609116	Single lumen	18G	16	25(21-29)	-	-
609109	Single lumen	18G	20	25(21-29)	-	-
609118	Single lumen	20G	5	10(8.5-11)	-	-
609119	Single lumen	20G	8	10(8.5-11)	-	-
609111	Single lumen	20G	13	10(8.5-11)	-	-
609112	Single lumen	20G	15	10(8.5-11)	-	-
609117	Single lumen	20G	16	10(8.5-11)	-	-
609113	Single lumen	20G	20	10(8.5-11)	-	-
609218	Double lumen	4F	5	14(12-16)	-	10(8.5-11)
609219	Double lumen	4F	8	14(12-16)	-	10(8.5-11)
609220	Double lumen	4F	13	14(12-16)	-	10(8.5-11)
609201	Double lumen	5F	8	21.5(18-25)	-	16.5(14-19)
609202	Double lumen	5F	13	21.5(18-25)	-	16.5(14-19)
609215	Double lumen	5F	10	21.5(18-25)	-	16.5(14-19)
609213	Double lumen	5F	15	21.5(18-25)	-	16.5(14-19)
609210	Double lumen	5F	16	21.5(18-25)	-	16.5(14-19)
609203	Double lumen	5F	20	21.5(18-25)	-	16.5(14-19)
* 609204	Double lumen	7F	15	85(72-98)	-	45(38-52)
* 609211	Double lumen	7F	16	85(72-98)	-	45(38-52)
609221	Double lumen	7F	18	85(72-98)	-	45(38-52)
* 609205	Double lumen	7F	20	85(72-98)	-	45(38-52)
609206	Double lumen	7F	30	85(72-98)	-	45(38-52)
609208	Double lumen	8F	11	95(81-109)	-	85(72-98)
609214	Double lumen	8F	15	95(81-109)	-	85(72-98)
609212	Double lumen	8F	16	95(81-109)	-	85(72-98)
609207	Double lumen	8F	20	95(81-109)	-	85(72-98)
609209	Double lumen	8F	30	95(81-109)	-	85(72-98)

Note:The code with * mark means main selling items.


Central Venous Catheter

Code	Lumen type	Size	Length (cm)	Distal	Middle	Proximal
609301	Triple lumen	5.5F	8	33(28-38)	6.5(5.5-7.4)	6.5(5.5-7.4)
609302	Triple lumen	5.5F	13	33(28-38)	6.5(5.5-7.4)	6.5(5.5-7.4)
609303	Triple lumen	5.5F	15	33(28-38)	6.5(5.5-7.4)	6.5(5.5-7.4)
609309	Triple lumen	5.5F	16	33(28-38)	6.5(5.5-7.4)	6.5(5.5-7.4)
609313	Triple lumen	5.5F	20	33(28-38)	6.5(5.5-7.4)	6.5(5.5-7.4)
* 609304	Triple lumen	7F	15	52(44-60)	26(22-30)	26(22-30)
* 609310	Triple lumen	7F	16	52(44-60)	26(22-30)	26(22-30)
609314	Triple lumen	7F	18	52(44-60)	26(22-30)	26(22-30)
* 609305	Triple lumen	7F	20	52(44-60)	26(22-30)	26(22-30)
609306	Triple lumen	7F	30	52(44-60)	26(22-30)	26(22-30)
609311	Triple lumen	8.5F	16	130(110-150)	33(28-38)	33(28-38)
609312	Triple lumen	8.5F	15	130(110-150)	33(28-38)	33(28-38)
609307	Triple lumen	8.5F	20	130(110-150)	33(28-38)	33(28-38)
609308	Triple lumen	8.5F	30	130(110-150)	33(28-38)	33(28-38)
609401	Quad lumen	8.5F	15	60(51-69)	Middle 1 100(85-115) Middle 2 30(25.5-35)	35(30-40)
609402	Quad lumen	8.5F	20	60(51-69)	Middle 1 100(85-115) Middle 2 30(25.5-35)	35(30-40)
609403	Quad lumen	8.5F	30	60(51-69)	Middle 1 100(85-115) Middle 2 30(25.5-35)	35(30-40)

Note:The code with * mark means main selling items.

Shun Lighthouse

Nitinol Guide Wire



Code	Size	Tip shape
626001	0. 018″*45cm	J tip
626002	0. 018″*50cm	J tip
626003	0. 018″*70cm	J tip
626004	0. 021″*45cm	J tip
626005	0. 021″*50cm	J tip
626006	0. 021″*70cm	J tip
626007	0. 035″*50cm	J tip
626008	0. 035″*60cm	J tip
626009	0. 035″*70cm	J tip
626010	0. 035″*150cm	Straight tip
626011	0. 038″*70cm	J tip
626012	0. 032″*60cm	J tip
626013	0. 032″*150cm	J tip
626014	0. 032″*150cm	Straight tip

Shun Pivot

Hemodialysis Catheter Kit



PRODUCT FEATURES :

- Excellent soft-tip to significantly reduce risk of vascular trauma
- With radiopaque materials, ensure correct placement of the catheter tip.
- Medical grade material: catheter automatically softens under the temperature of 37°

STANDARD KIT :

- Catheter
- Dilator
- Nitinol guide wire
- Introducer needle(straight or Y type)
- Scalpel
- Syringe(or blue guiding syringe)
- Injection caps



FLOW RATE:

Size(fr)	Lumen Tybe	The Distal Fiow Velocity	Center Hole Velocity	The Proximal Velocity
8	Single lumen	230	—	-
8	Double lumen	160	—	160
8. 5	Double lumen	160	—	160
9	Double lumen	180	—	180
11. 5	Double lumen	250	—	250
11	Double lumen	250	—	250
11. 5	Triple lumen	60	200	200
12	Triple lumen	60	200	200

Note: The actual flowrate should be above the value of 90% to 115%.

Code	Lumen type	Size	Extension Line	Length (cm)
610101	Single lumen	8	straight	10
610102	Single lumen	8	curved	10
610103	Single lumen	8	straight	13
610104	Single lumen	8	curved	13
610105	Single lumen	8	straight	16
610106	Single lumen	8	curved	16
610107	Single lumen	8	straight	20
610108	Single lumen	8	curved	20
610109	Single lumen	8	straight	30
610110	Single lumen	8	curved	30
610111	Single lumen	8	straight	15
610112	Single lumen	8	curved	15
610241	Double lumen	8.5	straight	13
610242	Double lumen	8.5	curved	13
610243	Double lumen	8.5	straight	16
610244	Double lumen	8.5	curved	16
610245	Double lumen	8.5	straight	20
610246	Double lumen	8.5	curved	20
610247	Double lumen	8.5	straight	11
610248	Double lumen	8.5	curved	11
610249	Double lumen	8.5	straight	12
610250	Double lumen	8.5	curved	12
610251	Double lumen	8.5	straight	15
610252	Double lumen	8.5	curved	15
610261	Double lumen	8	straight	12
610262	Double lumen	8	curved	12
610265	Double lumen	8	straight	13
610266	Double lumen	8	curved	13
610267	Double lumen	8	straight	15
610268	Double lumen	8	curved	15
610271	Double lumen	11	straight	13
610272	Double lumen	11	curved	13
610273	Double lumen	11	curved	15
610274	Double lumen	11	curved	15
610275	Double lumen	11	straight	16
610276	Double lumen	11	curved	16
610277	Double lumen	11	straight	20
610278	Double lumen	11	curved	20
610279	Double lumen	11	curved	12.5
610280	Double lumen	9	curved	10
610201	Double lumen	11.5	straight	13
610202	Double lumen	11.5	curved	13
* 610203	Double lumen	11.5	straight	15
* 610204	Double lumen	11.5	curved	15
* 610205	Double lumen	11.5	straight	16
* 610206	Double lumen	11.5	curved	16
* 610207	Double lumen	11.5	straight	20
* 610208	Double lumen	11.5	curved	20

Note:The code with * mark means main selling items.

Code	Lumen type	Size	Extension Line	Length (cm)
610209	Double lumen	11.5	straight	30
610210	Double lumen	11.5	curved	30
610211	Double lumen	11.5	straight	13.5
610212	Double lumen	11.5	curved	13.5
610213	Double lumen	11.5	straight	25
610214	Double lumen	11.5	curved	25
610215	Double lumen	11.5	straight	12.5
610216	Double lumen	11.5	curved	12.5
610264	Double lumen	11.5	pre-curved	15
610394	Double lumen	11.5	pre-curved	16
610221	Double lumen	12	straight	13
610222	Double lumen	12	curved	13
* 610223	Double lumen	12	straight	15
* 610224	Double lumen	12	curved	15
* 610225	Double lumen	12	straight	16
* 610226	Double lumen	12	curved	16
* 610227	Double lumen	12	straight	20
* 610228	Double lumen	12	curved	20
610229	Double lumen	12	straight	30
610230	Double lumen	12	curved	30
610231	Double lumen	12	straight	13.5
610232	Double lumen	12	curved	13.5
610233	Double lumen	12	straight	25
610234	Double lumen	12	curved	25
610235	Double lumen	12	straight	12
610236	Double lumen	12	curved	12
610263	Double lumen	12	pre-curved	15
610393	Double lumen	12	pre-curved	16
610395	Double lumen	9	straight	12
610396	Double lumen	9	straight	17
610397	Double lumen	12	pre-curved	20
610402	Double lumen	9	straight	10
610415	Double lumen	14	straight	25
610416	Double lumen	14	straight	30
610417	Double lumen	14	curved	25
610418	Double lumen	14	curved	30
610419	Double lumen	8	straight	20
610301	Triple lumen	11.5	straight	13
610302	Triple lumen	11.5	curved	13
610303	Triple lumen	11.5	straight	15
610304	Triple lumen	11.5	curved	15
610305	Triple lumen	11.5	straight	16
610306	Triple lumen	11.5	curved	16
* 610307	Triple lumen	11.5	straight	20
* 610308	Triple lumen	11.5	curved	20
610309	Triple lumen	11.5	straight	30
610310	Triple lumen	11.5	curved	30
610311	Triple lumen	11.5	straight	13.5
610312	Triple lumen	11.5	curved	13.5
610313	Triple lumen	11.5	straight	25
610314	Triple lumen	11.5	curved	25
610321	Triple lumen	12	straight	13
610322	Triple lumen	12	curved	13
610323	Triple lumen	12	straight	15
610324	Triple lumen	12	curved	15
610325	Triple lumen	12	straight	16
610326	Triple lumen	12	curved	16
* 610327	Triple lumen	12	straight	20
* 610328	Triple lumen	12	curved	20
610329	Triple lumen	12	straight	30
610330	Triple lumen	12	curved	30
610331	Triple lumen	12	straight	13.5
610332	Triple lumen	12	curved	13.5
610333	Triple lumen	12	straight	25
610334	Triple lumen	12	curved	25

Shun Stripe

Zebra Guidewire



Code	Size	Tip shape
626401	0. 032″*150cm	Angled tip
626402	0. 032″*150cm	Straight tip
* 626403	0. 035″*150cm	Angled tip
* 626404	0. 035″*150cm	Straight tip
* 626405	0. 035″*180cm	Angled tip
* 626406	0. 035″*180cm	Straight tip
626407	0. 035″*260cm	Angled tip
626408	0. 035″*260cm	Straight tip
* 626409	0. 038″*150cm	Angled tip
* 626410	0. 038″*150cm	Straight tip
626411	0. 032″*180cm	Angled tip
626412	0. 032″*180cm	Straight tip
626413	0. 032″*260cm	Angled tip
626414	0. 032″*260cm	Straight tip
* 626415	0. 038″*180cm	Angled tip
* 626416	0. 038″*180cm	Straight tip
626417	0. 038″*260cm	Angled tip
626418	0. 038″*260cm	Straight tip
626419	0. 032″*450cm	Angled tip
626420	0. 035″*450cm	Straight tip
626421	0. 035″*450cm	Angled tip
626422	0. 035″*450cm	Straight tip
626423	0. 038″*450cm	Angled tip
626424	0. 038″*450cm	Straight tip
626425	0.035 ″*120cm	Straight tip

Note:The code with * mark means main selling items.

Shun Route

Disposable Pressure Transducer



PRODUCT FEATURES :

- Consistent and accurate readings during monitoring.
- Ease-of-use with a variety of interface cables available.
- Fully integrated flow-thru component design simplifies filling and debubbling.
- Versatile,dual function Snap-Tap allows dynamic response testing.

Core part of DPT



Connector



- 1 Edward connector
- 2 Abbott connector
- 3 BD connector
- 4 Medex connector
- 5 Philips connector
- 6 USB connector
- 7 PVB connector
- 8 Utah connector
- 9 Mindray connector

Code	Connector	Description
* 612101	Edward	Single channel
612102	Philips	Single channel
* 612103	Abbott	Single channel
* 612104	BD	Single channel
* 612105	Utah	Single channel
612106	Medex	Single channel
612107	PVB SIMMS	Single channel
* 612108	USB	Single channel
612109	Mindray	Single channel
612201	Edward	Double channel
612202	Philips	Double channel
612203	Abbott	Double channel
612204	BD	Double channel
612205	Utah	Double channel
612206	Medex	Double channel
612207	PVB SIMMS	Double channel
612208	USB	Double channel
612209	Mindray	Double channel
612261	Edward	Core of DPT
612262	Philips	Core of DPT
612263	Abbott	Core of DPT
612264	BD	Core of DPT
612265	Utah	Core of DPT
612266	Medex	Core of DPT
612267	PVB SIMMS	Core of DPT
612268	USB	Core of DPT
612269	Mindray	Core of DPT

Note:The code with * mark means main selling items.

Shun Rocket

Angiographic Syringe



SINGLE SYRINGE SET



DOUBLE SYRINGE SET

ORDERING INFORMATION:

Application	Code	Specification	Capacity / ml	Applicable machine type	Components
CT	* 632112	CM-200	200	Medrad Stellant SX CT/ SCT121/SCT122	Single Syringe Set
	* 632114	CM-200/200	200/200	Medrad Stellant CT/ SCT1211/SCT212	Double Syringe Set
	* 632221	CM-200/200	200/200	LF CT9000 & CT 9000 ADV	Double Syringe Set
	* 632211	CM-200	200	LF CT9000 & CT 9000 ADV	Single Syringe Set
	632411	CM-200	200	Ezem Empower CT	Single Syringe Set
	632413	CM-200/200	200/200	Ezem Empower CTA	Double Syringe Set
	* 632230	CM-200	200	Medrad MCT/MCT Plus/ vistran CT/ En Vision CT	Single Syringe Set
	* 633225	CM-200/200	200/200	Medrad MCT/MCT Plus/ vistran CT/En Vision CT	Double Syringe Set
	* 632231	CM-200/200	200/200	Accutron CT/ Accutron CT-D/ Accutron MR/ Accutron HP-D,Medtron	Double Syringe Set
	* 632232	CM-200	200	Imaxeon salient	Single Syringe Set
	632282	CM-150	150	Imaxeon salient	Single Syringe Set
	632233	CM-200/200	200/200	Imaxeon salient	Double Syringe Set
	632234	CM-100	100	Nemoto A60/ A25/ Dual shot	Single Syringe Set
	632258	CM-100/200	100/200	Nemoto A60/ A25/ Dual shot	Double Syringe Set
	632235	CM-200	200	Nemoto A60/ Dual shot	Single Syringe Set
	632236	CM-200	200	Coeur	Single Syringe Set
	* 632414	CM-200	200	Accutron CT/ Accutron CT-D/ Accutron MR/ Accutron HP-D,Medtron	Single Syringe Set
	632212	CM-150	150	Angiomat iuumena	Single Syringe Set
	632113	CM-100/100	100/100	Nemoto A60/A25	Double Syringe Set

Note:The code with * mark means main selling items.

Angiographic Syringe

Application	Code	Specification	Capacity / ml	Applicable machine type	Components
MRI	632270	CM-50/50	50/50	Nemoto Dual Shot, Sonic Shot 50	Double Syringe Set
	632271	CM-60/100	60/100	Spectris@solaris	Double Syringe Set
	632237	CM-60/60	60/60	LF-Optistar MRI	Double Syringe Set
	632238	CM-65/65	65/65	Medrad Spectris MRI	Double Syringe Set
	632239	CM-115/65	115/65	Medrad Spectris Solaris MRI	Double Syringe Set
	632240	CM-60/60	60/60	Accutron MR	Double Syringe Set
	632241	CM-60/200	60/200	Accutron MR	Double Syringe Set
	632242	CM-25	25	Nemoto sonic shot 50	Single Syringe Set
	632244	CM-100/100	100/100	Acist Empower	Double Syringe Set
	632260	CM-50/50	50/50	Optistar Elite	Double Syringe Set
DSA	* 632259	CM-200	200	Medrad Mark V/ Mark V Plus/ Mark V ProVis	Single Syringe Set
	* 632122	CM-150	150	Medrad Mark V/ Mark V Plus/ Mark V ProVis	Single Syringe Set
	* 632257	CM-200	200	LF Angiomat 6000	Single Syringe Set
	* 632226	CM-150	150	LF Angiomat 6000	Single Syringe Set
	632227	CM-125	125	Nemoto120S	Single Syringe Set
	632228	CM-200	200	Accutron HP/ Accutron hp-d	Single Syringe Set
	632229	CM-150	150	Imaxeon Avadia	Single Syringe Set
CT/DSA	* 632222	CM-200	200	LF Angiomat Illumena	Single Syringe Set
	* 632224	CM-150	150	LF Angiomat Illumena	Single Syringe Set
CT/MRI	632243	CM-50	50	Nemoto Dual shot/ Sonic shot 50	Single Syringe Set

Note:The code with * mark means main selling items.

Accessories

Code	Description	Applicable machine type	Resistance to pressure
632245	Spiral connector tube	CT-200-MARK-E, CT-200-MARK, CT-200-LF, CT-200-MARK-S	300psi
632246	Connector tube	CT-100-NE	300psi
632247	T-connector tube	CT-200/200-Mark, MRI-100-MARK, MRI-60-MARK	300psi
632248	Y-Connector tube	CT-200/200-LF	300psi
632249	T-Connector tube	CT-200/200-LF, MRI-60-LF	300psi
632250	T-Connector tube	MRI-100-MARK, CT-200/200-MARK	300psi
632251	T-Connector tube	CT-200-MARK(E), CT-200-LF	300psi
632252	Quick fill tube	CT-200-MARK(E), CT-200-MARK, CT-200-LF	-
632253	Spike	CT-200/200-MARK, MRI-100-MARK	-
632254	Spike	MRI-100-MARK, MRI-60-MARK	-
632255	Spike	MRI-60-LF	-
632256	Prime tube	CT-200-MARK-S, CT-200/200-MARK	-
632280	-	150cm coiling tube	-
632281	-	Y coiling tube with two check valve,150cm	-