

64251 HLX

Halogen (< 75 V) Single End



Areas of application

- Microscopy
- Laboratory & Analysis
- UV Curing
- Fiber Illumination
- Surgical & Dental Overhead

Product features and benefits

- Precise filament alignment with patented quartz pinch technology
- HLX lamps provide 10% higher luminous flux with same power consumption over standard halogen
- Instant on and nearly constant luminous flux over the life of the lamp
- Dimmable



Technical data

General Product Information

| | |
|---------------------------|-----------------------------------|
| Product number (Americas) | 54021 |
| Product name (Americas) | 64251 HLX 20W 6V PG22 30/CS 1/SKU |
| Lamp type | HLX |
| ANSI code | - |
| LIF code | - |
| Global order reference | 64251 HLX |


Electrical Data

| | |
|-----------------|------|
| Nominal wattage | 20 W |
| Nominal voltage | 6 V |
| Type of current | AC |

Photometric Data

| | |
|---------------------------|-------------------------|
| Nominal luminous flux | 460 lm |
| Illuminated field | 2.3*0.6 mm ² |
| Color temperature | 3350 K |
| Color rendering index Ra | 100 |
| Light center length (LCL) | 14.0 mm |

Physical Attributes & Dimensions



| | |
|----------------|----------|
| Lamp base | PG22 |
| Diameter (in) | 0.354 in |
| Diameter | 9 mm |
| Length | 40.0 mm |
| Product weight | 4.70 g |

Operating Conditions

| | |
|------------------|-----|
| Burning position | Any |
|------------------|-----|

Lifetime Data

| | |
|------------------|--------|
| Nominal lifetime | 100 hr |
|------------------|--------|

Environmental & Regulatory Information

| | |
|---|------------------------------------|
| Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH) | |
| Primary article identifier | 4050300582290 4050300338316 |
| Declaration no. in SCIP database | No declarable substances contained |
| Candidate list substance 1 | No declarable substances contained |

Country specific information

| Product code | METEL code | SEG-No. | STK-Number | UK Org |
|---------------|--------------|---------|------------|--------|
| 4050300338316 | OSRH64251HLX | - | - | - |
| 4050300338316 | OSRH64251HLX | - | - | - |

Product datasheet

Safety advice

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (protective shields, grids, etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. There must also be a warning sign to indicate that the lamps give off high levels of heat. Detailed information is available on request.

Logistical Data

| Product code | Product description | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Volume | Gross weight |
|---------------|---------------------|---------------------------------|---|----------------------|--------------|
| 4050300338316 | 64251 HLX | Folding carton box 1 | 25 mm x 23 mm x 70 mm | 0.04 dm ³ | 11.00 g |
| 4050300338330 | 64251 HLX | Shipping carton box 30 | 163 mm x 124 mm x 84 mm | 1.70 dm ³ | 381.00 g |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.