



Langlebig, hoch flexibel und hochwertig
Durable, highly flexible and high quality

Verbesserter Korrosionsschutz
durch versilberte Litzen, auch bei unseren
bipolaren Modellen
Improved corrosion protection through
silver-plated strands, also with our bipolar
models



Bipolar

Geräteseite / Unit connecting



US-Modelle 2 Pol



Valleylab	3 m	92029	-	92019	92115
	5 m	92030	92196	92020	92094
Erbe VIO/ICC/ACC; Storz	3 m	92023	-	92015	92110
	5 m	92024	92190	92016	92111
Martin; Berchtold; Integra	3 m	92025	-	92017	92113
	5 m	92026	92192	92018	92092
Ellman	3 m	92204	-	-	92138
	5 m	-	-	-	-
Uniflex	3 m	92127	-	-	-
	5 m	92128	-	-	-
US-Modelle 2 Pol	3 m	92027	-	92021	92114
	5 m	92028	92194	92022	92093



Nicht konform mit der internationalen Norm IEC 60601-2-2:2010-01.
Nur an bipolaren Ausgang von Hochfrequenzgeneratoren anschließen.
Not conform with the international standard IEC 60601-2-2:2010-01.
Connect to bipolar output for high-frequency generators only.