

Laboratory Test report



226-TEST

NBN EN ISO/IEC 17025 :2017



R-Tech
Rue de Mons 3 – B-4000 Liège – Belgium
Tel.: +32 4 224 71 40 – Fax: +32 4 224 25 90
Member of Schröder Group

FORM L-54 Edition 01 - Revision 03 - Date : 20/05/2020

Tightness test

General information

Subject : VOLTANA EVO 1 - 16 Oslon Square Giant - Philips FP 75W - 1200mA - CL II (central screw modified 1Nm)

Asked by : SZÜGYI János Péter

Created on : 08/01/2021

Started on : 11/01/2021

Test number : D210026

Reference norm : IEC/EN 60598-1 Standard

Sample(s) : E210017

Folder : P-F21002

Test conditions

Luminaire : VOLTANA EVO 1

Number of LED : 16

LED : Osram OSLON SQUARE GIANT

Driver current (mA) : 1200

Protector Material : PC

Operator : Philippe Léonard



IMG_7592

Conclusion



Success

Conclusion :

According section 9.2 of IEC 60598-1:2014, AMD1:2017 :

IP66 passed.

Validated by :
GHYSENS Gilles

Duplicate to : SZÜGYI János Péter, HORVÁTH Csaba, CSIKÓS
Balázs, BEDŐ Péter
LAB : 15/02/2021

D210026

1/4

Test(s) details

Test(s)

Name	Description	Result
IP6x	- Luminaire switched ON until stable T° - Talcum in suspension (blowing ON) - After 1', luminaire OFF - Talcum for 3 hours	Success
IPx6	- Luminaire switched ON until stable T° - Luminaire switched OFF and immediately sprayed with water jet - Hose diam. 12,5 mm - Water flow: 100 l/min - Spraying distance: 3 m - Duration of test: 3 minutes	Success

IP6x

Result(s)

Pre-conditioning time :

- 60minutes

Test result :

- Passed : No talcum entry in the enclosure of the luminaire
-

IPx6

Result(s)

Pre-conditioning time :

- 60 minutes

Test result :

- Passed : No water entry in the enclosure of the luminaire

Test room temperature (°C) :

23.2

Measurement equipment :

Talcum chamber (A003)
Thermometer (A039/2)
Rotating table (A001/2)
Chronometer (A043/3)
Thermometer (A039/1)
Flowmeter (A001/10)
IPx6 nozzle (A001/5)

Quantities measured :

Verification of water/dust ingress within a luminaire enclosure according to

For IP2X: PT-S-14
For IP3X/4X: PT-S-15
For IP5X/6X: PT-S-06
For IPX3/X4: PT-S-01
For IPX5/X6: PT-S-08
For IPX7/X8: PT-S-09

Uncertainties :

Statement of uncertainties (K=2, 95% of confidence level):

Time: 0,35 seconds per 10 minutes

Temperature: 0,6 °K

Calipers: 0,005 mm

Measuring tape: $\pm 1,13$ mm

Dynamometric key :

From 0.5 to 2.5 Nm : 0,15 Nm

From 2.5 to 5 Nm : 0,22 Nm

From 5 to 25 Nm : 0,83 Nm

From 25 to 60 Nm : 2,73 Nm

From 60 to 100 Nm : 3,55 Nm

For solid ingress test:

IP2X:

Probe dimensions: $\pm 0,6$ mm

Applied force: $\pm 0,4$ N

IP3X:

Probe dimensions: $\pm 0,3$ mm

Applied force: $\pm 0,13$ N

IP4X:

Probe dimensions: $\pm 0,1$ mm

Applied force: $\pm 0,11$ N

IP5X/6X

Test duration (talcum suspension time): ± 3 seconds

Talcum mass: 0,02 %

For liquid ingress test:

IPX3/X4

Table rotation: ± 6 sec/rotation

Arms Rotation angle: $\pm 3^\circ$

Water flow: ± 4 %

IPX5/X6

Table rotation: ± 6 sec/rotation

Water flow: ± 4 %

Test Distance: +0 / -50 cm

IPX7/X8

Test depth: +10 cm / -0 cm

Decision rules :

Pass/fail criteria

For solid ingress test:

IP2X:

If contact possible with live parts: fail

Otherwise: pass

IP3X/4X:

For luminaires without draining holes, nor ventilation slots for forced cooling, penetration of the test probe in the enclosure: fail

For luminaires with draining holes, or ventilation slots for forced cooling, if contact possible with live part: fail

Otherwise: pass

IP5X/6X

By visual inspection:

If possible hazard due to presence of conductive dust: fail

If no possible hazard due to the presence of conductive dust: IP5X granted

No presence of talcum: IP6X granted

For liquid ingress test:

IPX3/X4/X5/X6:

By visual inspection:

If possible hazard due to presence of water: fail

If no possible hazard due to the presence of water and no efficient way to evacuate the water: fail

If no possible hazard due to the presence of water and an efficient way to evacuate the water: pass

No presence of water: pass

IPX7/X8:

By visual inspection:

Presence of water: fail

No presence of water: pass

End of accredited report :
