




## COLD LIGHT CABLES / HTT CABLES

20% more light transmission  
than with standard cables



## HTT-CABLES

High Transmission Technology  
Assembled fibres




Length	Diameter	without fittings	incl. RUDOLF / Storz fittings
		Ordering no.	
1.8 m	3.5 mm	IM201-180	IM201-1811
2.3 m	3.5 mm	IM201-230	IM201-2311
<b>3.0 m</b>	<b>3.5 mm</b>	IM201-300	<b>IM201-3011</b>
1.8 m	4.8 mm	IM202-180	IM202-1811
2.3 m	4.8 mm	IM202-230	IM202-2311
3.0 m	4.8 mm	IM202-301	IM202-3011




For endoscope < Ø 5 mm → light cable Ø 3.5 mm  
For endoscope > Ø 5 mm → light cable Ø 4.8 mm



## FITTINGS FOR COLD LIGHT CABLES



<b>Adapter Endoscope Side (Light Output)</b>	<b>Connection</b>	<b>Ordering no.</b>
RUDOLF / Storz		IM220-020
<b>Wolf (Snap-In)</b>		<b>IM220-021</b>
ACMI (Snap-In)		IM220-022
Stryker		IM220-025



<b>Adapter Light Source Side (Light Input)</b>	<b>Connection</b>	<b>Ordering no.</b>
RUDOLF / Storz		IM220-040
<b>Wolf</b>		<b>IM220-041</b>
ACMI		IM220-042
Olympus		IM220-043