

# Ureter working channel Access Sheath Standard

Made of Polyurethane  
Dilator: PEBAX  
Tecoflex® USA

Provides **ureteral dilation** and  
a **continuous working channel**  
for the introduction of Endoscopes  
and Instruments during ureteral  
access procedures.



Art. No.	Sheath Inner Diameter		Sheath Length cm
	Ø (Fr/CH)	= mm	
<b>UAS 10-13</b>	10	= 3.3	13
<b>UAS 10-20</b>	10	= 3.3	20
<b>UAS 10-28</b>	10	= 3.3	28
<b>UAS 10-30</b>	10	= 3.3	30
<b>UAS 10-35</b>	10	= 3.3	35
<b>UAS 10-45</b>	10	= 3.3	45
<b>UAS 12-13</b>	12	= 4	13
<b>UAS 12-20</b>	12	= 4	20
<b>UAS 12-28</b>	12	= 4	28
<b>UAS 12-30</b>	12	= 4	30
<b>UAS 12-35</b>	12	= 4	35
<b>UAS 12-45</b>	12	= 4	45
<b>UAS 14-13</b>	14	= 4.7	13
<b>UAS 14-20</b>	14	= 4.7	20
<b>UAS 14-28</b>	14	= 4.7	28
<b>UAS 14-30</b>	14	= 4.7	30
<b>UAS 14-35</b>	14	= 4.7	35
<b>UAS 14-45</b>	14	= 4.7	45