

CONFIGURATION SUMMARY REPORT

SIEMENS REPRESENTATIVE

George Surdu

Quote Name: Acuson Juniper 3 child Hospital

Included products are listed below:

Qty	Part No.	Item Description	B Text
1	11361954	JUNIPER, BASE CONFIGURATION	The ACUSON Juniper ultrasound system is a high-performance, compact diagnostic ultrasound system that provides embedded time-tested and leading-edge imaging technologies encapsulated by an elegant, yet simple and intuitive design. With a capacitive touch screen and traditional control panel, the ACUSON Juniper system is engineered to grow and adapt with dynamic user requirements and departmental demands as they evolve.
1	11335807	JUNIPER, VA10, OPER SYS, INTL ENG	Product-specific operating software, VA10 software, control panel overlay and detailed instructions for use in English.
1	11335825	JUNIPER, WORLDWIDE KEYBOARD	
1	11235416	CORDSET, 230V, GERMAN	Schuko-style custom cordset and plug. Valid only with 230V fuse. Cordset also compatible for use in Austria, Bolivia, Brazil, Bulgaria, Chile, Estonia, Finland, Germany, Greece, Hungary, Korea, Latvia, Lithuania, Luxembourg, Netherlands, Norway, Poland, Portugal, Romania, Russia, Saudi Arabia, Slovenia, Sweden, Turkey, and Ukraine.

CONFIGURATION SUMMARY REPORT

SIEMENS REPRESENTATIVE

George Surdu

1 11361712

JUNIPER, ESIETOUCH

eSie Touch elasticity imaging is a real-time quantitative imaging method that calculates and displays the relative stiffness of the tissue.

It is available for breast and thyroid exams on the 11L4, 12L3, 16L4 and 18H5 (only has thyroid) transducers.

eSie Touch elasticity imaging allows the user to generate the elastogram by applying gentle sequential compression cycles during standard B-mode imaging. This relative displacement of tissue is displayed as an elastogram in a live dual image display of the grayscale or color image with the standard B-mode image.

-Unique mapping options in grayscale and color further enhance the ease of interpreting an elastogram

-Area, distance and strain ratio measurement capability allow for quantitative comparison of two images

-A quality factor indication provides feedback on the quality of acquisition and allows more acute selection of most appropriate frame(s) for assessment or measurement

eSie Touch elasticity imaging is available as a standalone option.

1 11292173

ESIEPREP SRS PRECONFIGURATION

To simplify the connection to Smart Remote Services (SRS), the eSiePrep option offers factory pre-configuration of Internet Based Connectivity (IBC) settings. eSiePrep

CONFIGURATION SUMMARY REPORT

SIEMENS REPRESENTATIVE

George Surdu

enables an SRS connection without additional on-site configuration for systems using an internet-based, non-VPN network.

IBC allows customer systems to be connected to the secure SRS portal based on an internet connection without any further hardware requirement or IP address dependency. This approach offers greater system mobility while maintaining SRS connectivity.

1	11335891	JUNIPER, TRANSDUCER, 8V4, TC-ZIF	8V4 Vector transducer.
1	11335921	JUNIPER, TRANSDUCER, 16L4, TC-ZIF	16L4 Linear transducer.
1	11335902	JUNIPER, TRANSDUCER, 7C2, TC-ZIF	7C2 Curvilinear transducer.
1	11361729	DVD ROM	Digital versatile disc-read/write memory (DVD-ROM) is a read/write DVD (digital versatile disc) commonly used for storing large image data.
1	11335928	PRINTER (USB) BW, FRONT, MTS	The Mitsubishi P95DW is a USB-connected high-performance thermal printer that provides high-quality grayscale prints. Mitsubishi P95DW-DC - B/W digital printer, UL/CE-approved.
1	11361533	JUNIPER VA10, INST. FOR USE, RUM	General overview and technical description of the ultrasound imaging system operating instructions written in Romanian.