### Monofocal IOLs

### **Aspheric HP IOLs**



	SeeLens HP *	BunnyLens HP *
Platform	C-Loop	4 - Loop
Overall Diameter	13 mm	11 mm (>10D) 11.5mm (≤10D)
Placement	Capsular Bag	
Optic diameter	6 mm	
Power range	+5.0 to +10.0 (1D increments) +10.5 to +30.0 (0.5D increments) +31.0 to +35.0 (1D increments)	
Optic design	Aspheric	
360° Continuous Square Edge	Yes	
Haptic angulation	5°	
Material	Hydrophobic acrylic with bonded UV absorber and violet light filter	
Refractive Index	1.48 (@ 35°c)	
A-constant (SKR/T) for Optical or Immersion US biometry	119	118.9
A-constant (SKR/T) for Contact US biometry	118.5	118.4
Sterilization	ETO	


# Providing Excellent Vision Quality For Your Patient

## The Aspheric HP IOLs were designed by the most advanced optical tools to provide:

- reduced spherical aberration
- · functional vision in night conditions

The Aspheric Hydrophobic lens from Hanita Lenses, provides the patient with an excellent vision quality at day and night conditions, by using state-of-the-art aberration free Aspherical optical design.

### **Stability and Centration**



#### PRELOADED HYDROPHOBIC IOL SYSTEM

- Simplifying cataract surgery
- Ready for implant
- Smooth and EASY injection through a 2.2 mm incision

