Monofocal IOLs

Aspheric HP IOLs



| | SeeLens HP * | BunnyLens HP * |
|---|---|-------------------------------|
| Platform | C-Loop | 4 - Loop |
| Overall Diameter | 13 mm | 11 mm (>10D) 11.5mm (≤10D) |
| Placement | Capsular Bag | |
| Optic diameter | 6 mm | |
| Power range | +5.0 to +10.0 (1D increments) +10.5 to +30.0 (0.5D increments) +31.0 to +35.0 (1D increments) | |
| Optic design | Aspheric | |
| 360° Continuous Square Edge | Yes | |
| Haptic angulation | 5° | |
| Material | Hydrophobic acrylic with bonded UV absorber and violet light filter | |
| Refractive Index | 1.48 (@ 35°c) | |
| A-constant (SKR/T) for Optical or Immersion US biometry | 119 | 118.9 |
| A-constant (SKR/T) for Contact US biometry | 118.5 | 118.4 |
| Sterilization | ETO | |


Providing Excellent Vision Quality For Your Patient

The Aspheric HP IOLs were designed by the most advanced optical tools to provide:

- reduced spherical aberration
- · functional vision in night conditions

The Aspheric Hydrophobic lens from Hanita Lenses, provides the patient with an excellent vision quality at day and night conditions, by using state-of-the-art aberration free Aspherical optical design.

Stability and Centration



PRELOADED HYDROPHOBIC IOL SYSTEM

- Simplifying cataract surgery
- Ready for implant
- Smooth and EASY injection through a 2.2 mm incision

