




Teknokroma Capillary Columns

TRB-35

35% Diphenyl - 65% Dimethyl polysiloxane, bonded and crosslinked phase.

- 35% Diphenyl- 65% dimethyl polysiloxane
- Column of intermediate polarity without cyanopropyl groups in its structure
- Excellent confirmation column



Structure of Poly (dimethyldiphenyl) siloxane

TRB-35 Equivalent Phase

Agilent: HP-35, DB-35

Supelco: SPB-35


Restek: Rtx-35

SGE: BPX-35

Quadrex: 007-11

TRB-35

InternalLength		Film	Temp	Part.
Diam.(mm)	(m)	Thickness (µm)	limits (°C)	N°. (P/N)
0,25	15	0,15	-20 to 300/320	TR-351312
	15	0,25	-20 to 300/320	TR-350212
	30	0,15	-20 to 300/320	TR-351332
	30	0,25	-20 to 300/320	TR-350232
	60	0,15	-20 to 300/320	TR-351362
	60	0,25	-20 to 300/320	TR-350262
0,32	15	0,15	-20 to 300/320	TR-351313
	15	0,25	-20 to 300/320	TR-350213
	15	0,50	-20 to 290/310	TR-350513
	30	0,15	-20 to 300/320	TR-351333
	30	0,25	-20 to 300/320	TR-350233
	30	0,50	-20 to 290/310	TR-350533
	60	0,15	-20 to 300/320	TR-351363
	60	0,25	-20 to 300/320	TR-350263
	60	0,50	-20 to 290/310	TR-350563
0,53	15	0,50	-20 to 260/280	TR-350515
	15	1,00	-20 to 260/280	TR-351015
	30	0,50	-20 to 260/280	TR-350535
	30	1,00	-20 to 260/280	TR-351035
	60	0,50	-20 to 260/280	TR-350565
	60	1,00	-20 to 260/280	TR-351065



TKG 1125