

LEADING THE WAY IN GUIDE WIRE TECHNOLOGY

BIFURCATIONS

TRACKING ACROSS
steep angulated takeoffs

TORTUOUS VESSELS

FULL POLYMER COVER
for smooth tracking

CALCIFIED LESIONS

POLYMER COVER AND
HYDROPHILIC COATING
for outstanding lubricity

CTOs

NAVIGATING LESIONS
WITH PILOT 50

PENETRATING LESIONS
WITH PILOT 200

ABBOTT GUIDE WIRES
SPECIALTY



HI-TORQUE

PILOT

GUIDE WIRES

The right tool for a
“soft” approach



HI-TORQUE PILOT ORDERING INFORMATION

HI-TORQUE PILOT 50	COVER	TIP LOAD	COATING	CORE	TIP STYLE
	FULL POLYMER	1.5g	HYDROPHILIC	DURASTEEL STAINLESS STEEL	CORE-TO-TIP

PRODUCT DESCRIPTION	PART NUMBER	WIRE LENGTH (cm)	TIP SHAPE	RADIOPAQUE TIP LENGTH (cm)	PENETRATION POWER (kg/in ²)
HI-TORQUE PILOT 50	1010480-H	190	Straight	3	10
HI-TORQUE PILOT 50	1010480-HJ	190	J	3	10
HI-TORQUE PILOT 50	1010483-H	300	Straight	3	10
HI-TORQUE PILOT 50	1010483-HJ	300	J	3	10

HI-TORQUE PILOT 150	COVER	TIP LOAD	COATING	CORE	TIP STYLE
	FULL POLYMER	2.7g	HYDROPHILIC	DURASTEEL STAINLESS STEEL	CORE-TO-TIP

PRODUCT DESCRIPTION	PART NUMBER	WIRE LENGTH (cm)	TIP SHAPE	RADIOPAQUE TIP LENGTH (cm)	PENETRATION POWER (kg/in ²)
HI-TORQUE PILOT 150	1010481-H	190	Straight	3	20
HI-TORQUE PILOT 150	1010481-HJ	190	J	3	20
HI-TORQUE PILOT 150	1010484-H	300	Straight	3	20
HI-TORQUE PILOT 150	1010484-HJ	300	J	3	20

HI-TORQUE PILOT 200	COVER	TIP LOAD	COATING	CORE	TIP STYLE
	FULL POLYMER	4.1g	HYDROPHILIC	DURASTEEL STAINLESS STEEL	CORE-TO-TIP

PRODUCT DESCRIPTION	PART NUMBER	WIRE LENGTH (cm)	TIP SHAPE	RADIOPAQUE TIP LENGTH (cm)	PENETRATION POWER (kg/in ²)
HI-TORQUE PILOT 200	1010482-H	190	Straight	3	30
HI-TORQUE PILOT 200	1010482-HJ	190	J	3	30
HI-TORQUE PILOT 200	1010485-H	300	Straight	3	30
HI-TORQUE PILOT 200	1010485-HJ	300	J	3	30

3 cm RADIOPAQUE COILS

CORE-TO-TIP DESIGN
for precise steering and tip control

GOLD MARKER
4.5 cm from tip

RESPONSEASE TRANSITIONLESS CORE GRIND
for excellent tracking and 1:1 torque response

DURASTEEL HIGH TENSILE STRENGTH STAINLESS STEEL CORE MATERIAL
for durability and superb torque control

PTFE COATING

FULL POLYMER COVER AND HYDROPHILIC COATING
for long-lasting lubricity

Caution: These products are intended for use by or under the direction of a physician. Prior to use, reference the Instructions for Use provided inside the product carton (when available), at eifu.abbottvascular.com or at Manuals.sjm.com for more detailed information on Indications, Contraindications, Warnings, Precautions and Adverse Events. **Information contained herein for distribution outside the U.S. only.** Check the regulatory status of the device in areas where CE marking is not the regulation in force.

Tests performed by and data on file at Abbott. Illustrations are artist's representations only and should not be considered as engineering drawings or photographs.

Abbott International BVBA

Park Lane, Culliganlaan 2B, 1831 Diegem, Belgium, Tel: 32.2.714.14.11

HI-TORQUE PILOT, HI-TORQUE PILOT 50, HI-TORQUE PILOT 150, and HI-TORQUE PILOT 200 are trademarks of the Abbott Group of Companies.

www.Vascular.Abbott

©2018 Abbott. All rights reserved. AP2945211-OUS Rev. A



