

TECHNICAL FEATURES

MAGNETOMED 7200 MA1331		
Power supply		230 Vac 50-60 Hz $\pm 10\%$
		115 Vac 50-60 Hz $\pm 10\%$ *
Maximum Absorbed power	MAGNETOMED 7200	450 VA
Double fuse protection (T)	MAGNETOMED 7200	3.15 A - T - 5 x 20 mm for 230Vac supply 6.3 A - T. – 5 x 20 mm for 115 Vac supply
Backlit LCD display to view and check the operating parameters		graphic 320 x 240 pixel touch screen + encoder
Programmable treatment time		Up to 99 minutes
<u>Duty Cycle adjustable</u>		<u>(10÷100) %</u>
Programmable treatment frequency		(1 - 100)Hz
<u>Electrical insulation class / applied parts in compliance with the UNI EN 60601-1 standard</u>		<u>I/BF</u>
<u>Device class in compliance with the 93/42/CEE directive</u>		<u>II A</u>
<u>Degree of protection against the input of liquids according to the UNI EN 60601-1 standard</u>		<u>IPX0</u>
Maximum induction		100 Gauss $\pm 20\%$
Output channels	MAGNETOMED 7200	2 independent
Stored protocols		81

TECHNICAL FEATURES

Storable protocols in the smart-card		200
Storable protocols in the user memory		200
Magnetomed 7000 series : plastic desktop container , external size (width x height x depth)	MAGNETOMED 7200	39 x H14 x 30 cm
Unit body weight	MAGNETOMED 7200	3,9 Kg
<u>Conditions for use</u>	<u>Room temperature</u>	<u>(+10 ÷ +40) °C</u>
	<u>Relative humidity</u>	<u>(10 ÷ 80) % without condensation</u>
<u>Conditions for stocking / transport</u>	<u>Room temperature</u>	<u>(-40 ÷ +70) °C</u>
	<u>Relative humidity</u>	<u>(10 ÷ 100) % without condensation</u>
	<u>Atmospheric pressure</u>	<u>(500 ÷ 1060) hPa</u>

*upon request