Instrumentation



8404ZXK

C-MAC® HD Monitor for CMOS Endoscopes,

screen size 8" with 1920 x 1200 pixel resolution, two camera inputs, a USB and HDMI port, optimized user interface with touch screen, video and image capture in real time on SD card, playback of recorded video clips and still images, data transfer from SD card to USB flash drive possible, splash-proof according to IP54, suitable for wipe disinfection, shock-resistant ABS plastic housing, intelligent power management with rechargeable Li-ion batteries, VESA 75 mounting option, mains adaptor for EU, UK, USA and Australia, power supply 110-240 VAC, 50/60 Hz, for use with CMOS videoendoscopes including:

Protection Cap VESA 75 Quick Clip Power Supply Set SD Card Ultra, 16 GB



8403X

C-MAC® Connecting Cable, with C-MAC® system interface, for C-MAC® Monitors 8403ZXK, 8404ZXK, length 200 cm, for use with C-MAC® Video Laryngoscopes 8403/8404xxx



8403XA

C-MAC® Extension Cable, for the transmission of analog and digital signals, dustproof according to IP50 standards (not waterproof), length 200 cm, for use with C-MAC® Monitor 8404ZX, in conjunction with all endoscopes of the KARL STORZ Office Line (8-pin instruments)



8403XDK

C-MAC® POCKET MONITOR Set, unit with LCD monitor and power supply for all C-MAC® video laryngoscopes, with C-MAC® system interface, screen size 3.5", documentation of images and video sequences saved on internal memory, monitor movable via two rotation axes, rechargeable Li-Ion battery, 1 h operation time, exchangeable battery pack, 2 h charging time, power management with capacity indicator, protection class IPX8, for use with C-MAC® Video Laryngoscopes 8403/8404xxx including:

Battery, rechargeable
USB Data Cable
Protection Cap, for reprocessing

Overview of the new flexible single-use video endoscopes



STERILE (2)

091330-06* Video Rhino-Laryngoscope, sterile, for single use, package of 6, for use with E-BOX TP012, direction of view 0°, angle of view 90°, working length 30 cm, outer diameter 3.5 mm, deflection up/down 140°/140°



STERILE (2)



091370-06* Video Esophagoscope, sterile, for single use, package of 6, for use with E-BOX TP012, direction of view 0°, angle of view 90°, working length 75 cm, outer diameter 3.5 mm, deflection up/down 210°/140°



TP012

E-BOX, for flexible video endoscopes for single use, compatible with C-MAC® Monitor 8403ZX and C-HUB® II 20290320

NEW

Video Uretero-Renoscopes






Situations where the use of single-use endoscopes may be recommended:

- Highly infectious patients
- Clinics without in-house reprocessing departments
- Irregular use of flexible endoscopes
- Backup for reusable endoscopes

Special Features:

- CMOS chip and LED light source at the distal end of the endoscope
- Product is sterile on delivery and ready for immediate use





091271-06

Video Uretero-Renoscope FLEX-X^{C1}, with positive deflection mechanism, sterile, for single use, package of 6, for use with E-Box TP 012, E-Box TC 028, TELE PACK+

TP 101, TELECAM C3 TC 100

Direction of view: 0°

Angle of view: 90°

Working length: 70 cm

Outer diameter: 8.5 Fr.

Working channel diameter: 3.6 Fr.

Deflection up/down: 270°/270°

091279-06

Video Uretero-Renoscope FLEX-X^{C1}, with contrapositive deflection mechanism, sterile, for single use, package of 6, for use with E-Box TP 012, E-Box TC 028, TELE PACK+

TP 101, TELECAM C3 TC 100

Direction of view: 0°

Angle of view: 90°

Working length: 70 cm

Outer diameter: 8.5 Fr.

Working channel diameter: 3.6 Fr.

Deflection up/down: 270°/270°

183



UG914

COR Airway Mobile Stand, high, rides on 4 antistatic dual wheels, with locking brakes, high beam module, incl. cable manager and handle,

consisting of:

UG804 **Subrack,** COR mobile stand, high
UG811 **Top Cover Monitor Holder,** COR mobile

stand

UG815 **Equipment Rail,** COR mobile stand UG854 **Stainless Steel Tube,** COR mobile stand,

length 400 mm

UG857 **Monitor Module,** COR mobile stand UG862 **Drawer,** wide, COR mobile stand



UG915

COR C-MAC® Mobile Stand, high, rides on 4 antistatic dual wheels, with locking brakes, high beam module, incl. cable manager and handle,

consisting of:

UG804 **Subrack,** COR mobile stand, high
UG811 **Top Cover Monitor Holder,** COR mobile

stand

UG815 **Equipment Rail,** COR mobile stand UG862 **Drawer,** wide, COR mobile stand

UG854 Stainless Steel Tube, COR mobile stand,

length 400 mm

ET43-303127 Cross Tube Adaptor

ET43-302703 Stainless Steel Round Pipe,

length 250 mm