

Easy to Install, Ergonomic and Reliable

Haier are pioneers in under-counter pharmacy refrigerator design and manufacturing, offering ultra-low noise system, safety lock, complete alarm system for sample safety and protection.



HYC-118

HYC-118A

Reliability and Key Features



- Energy efficient hydrocarbon (HC) refrigeration system
- Permanently lubricated cooling fan for safety and longevity
- Forced-air cooling with optimized air distribution system designed to achieve maximum temperature uniformity and stability
- Optimized refrigeration system design for more effective cooling and speedy recovery
- Temperature variation within $\pm 3^{\circ}\text{C}$
- Chamber temperature range $2\text{--}8^{\circ}\text{C}$
- Microprocessor control, digital display and temperature adjustment with an increment of 0.1°C
- Designed for ambient temperature $10\text{--}32^{\circ}\text{C}$ with humidity below 70%

Safety

- Equipped with a complete temperature alarm system featuring audible buzzer and visual flashing light
- Capable of alerting failures due to high and low temperature, sensor error, door ajar, power failure, and remote alarm interface

Ergonomic Design

- Interior LED light
- Safety lock to prevent unauthorized access



Specifications



Model	HYC-68		HYC-68A		HYC-118		HYC-118A		HYC-290		HYC-390		HYC-410		HYC-639		HYC-390F		HYC-610		HYC-940		HYC-940F		HYC-1378			
Technical Data	Cabinet Type	Upright, Solid Door		Upright, Glass Door		Upright, Solid Door		Upright, Glass Door		Upright, Single Door		Upright, Single Door		Upright, single door		Upright, glass door		Upright, Single Door		Upright, Single Door		Upright, Double Glass Door		Upright, Double Solid Door		Upright, double door		
	Climate Class	N		N		N		N		N		N		N		ST		N		N		N		N		N		
	Cooling Type	Forced Air Cooling		Forced Air Cooling		Forced Air Cooling		Forced Air Cooling		Forced Air Cooling		Forced Air Cooling		Forced air cooling		Forced air cooling		Forced Air cooling		Forced Air Cooling		Forced Air Cooling		Forced Air Cooling		Forced Air Cooling		
	Defrost Mode	Auto		Auto		Auto		Auto		Auto		Auto		Auto		Auto		Auto		Auto		Auto		Auto		Auto		
	Refrigerant	HC		HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	HC	
	Sound Level (dB(A))	41		41		41		41		43	43	43	43	41	43	43	43	43	43	45	43	45	43	45	43	43	45	
Performance	Temperature Range (°C)	2-8		2-8		2-8		2-8		2-8		2-8		2-8		2-8		2-8		2-8		2-8		2-8		2-8		
Control	Controller	Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		Microprocessor		
	Display	LED		LED		LED		LED		LED		LED		LED		LED		LED		LED		LED		LED		LED		
Electrical Data	Power Supply (V/Hz)	220-240/50	115/60	220-240/50	115/60	220-240/50/60	115/60	220-240/50/60	115/60	220-240/50/60	115/60	220-240/50/60	115/60	220-240/50	220-240/50	220-240/50/60	115/60	220-240/50/60	115/60	220-240/50/60	115/60	220-240/50/60	115/60	220-240/50/60	220-240/50/60	115/60	220-240/50/60	115/60
	Power (W)	140	150	140	150	190	190	230	230	200	350	240	360	350	410	210	115	550	500	700	850	500	850	500	600	850	600	850
	Electrical Current (A)	0.85	1.7	0.85	1.7	1.4	1.4	1.5	1.5	2.2	1.8	2.4	1.8	2.0	2.15	1	1.5	3	6.2	3.5	7.5	2.7	7.5	2.7	3	7.5	3	7.5
Dimensions	Capacity (L/Cu.Ft)	68/2.4		68/2.4		118/4.2		118/4.2		290/10.2		390/13.8		410		639/28.3		390/13.8		610/21.6		890/31.4		890/31.4		1378/48.7		
	Net/Gross Weight (approx)	kg		kg		kg		kg		kg		kg		kg		kg		kg		kg		kg		kg		kg		
		lbs		lbs		lbs		lbs		lbs		lbs		lbs		lbs		lbs		lbs		lbs		lbs		lbs		
	Interior Dimensions (W*D*H)	mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		
		in		in		in		in		in		in		in		in		in		in		in		in		in		
	Exterior Dimensions (W*D*H)	mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		
		in		in		in		in		in		in		in		in		in		in		in		in		in		
	Packing Dimensions (W*D*H)	mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		mm		
		in		in		in		in		in		in		in		in		in		in		in		in		in		
	Container Load (20'/40'/40'H)	108/228/228		108/228/228		48/102/102		48/102/102		21/42/42		21/42/42		23/48/48		12/26/26		21/42/42		12/26/26		8/18/18		8/18/18		6/12/12		
Alarms	High/Low Temperature	Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		
	Remote Alarm	Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		
	Power Failure	Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		
	Sensor Error	Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		
	Low Battery	Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		
	Door Ajar	Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		Y		
Accessories	Caster	Y		Y		Y		Y		Y		Y		4		4		Y		Y		Y		Y		Y		
	Foot	Y		Y		Y		Y		Y		Y		2		2		Y		Y		Y		Y		Y		
	Porthole	Y		Y		Y		Y		Y		Y		Y		1		Y		Y		Y		Y		Y		
	Shelves/Drawers	2/1		2/1		3/1		3/1		5/-		7/-		6		4(6 optional)		7/-		6/-		12/-		12/-		12/-		
	USB Interface	Optional		Optional		/		/		Y		Optional		Optional		Y		Optional		Y		Optional		Optional		Optional		
	Printer	N/A		N/A		N/A		N/A		Optional		Optional		Optional		Optional		Optional		N/A		Optional		Optional		Optional		
	Temperature Recorder	N/A		N/A		N/A		N/A		Optional		Optional		N/A		N/A		Optional		Optional		Optional		Optional		Optional		
Others	Certification	CE	UL	CE	UL	CE	UL	CE	UL	UL	CE	UL	CE	ENERGY STAR	CE	ENERGY STAR	CE	ENERGY STAR	CE	UL	CE	UL	CE	UL	CE	CE	UL	