

	iRay 奕瑞	Doc ID	042-501-01
		Version	A7
	Mars1417X Product Specification	Revision Date	2022-08-11
		Page	1 / 4

Mars1417X Product Specification

Content

1. Product Description and Feature	2
2. Basic Technical Specification	2
3. Image Performance	2
4. Workflow	3
5. Environmental Requirement	3
6. Detector Reference Drawing	4

	iRay 奕瑞	Doc ID	042-501-01
		Version	A7
	Mars1417X Product Specification	Revision Date	2022-08-11
		Page	2 / 4

1. Product Description and Feature

Mars1417X is a 14x17 cassette-size wireless portable flat panel detector designed for Human used digital radiography.

- Fast workflow
- More image details
- Excellent image quality
- Cassette-size flat panel detector

2. Basic Technical Specification

Detector Technology	Amorphous Silicon
Scintillator	CsI
Active Area	350mm × 430mm
Number of Pixels	3500 × 4300
Pixel Pitch	100μm
AD Conversion	16 bit
Trigger Mode	AED (Optional) /Software
Data Interface	Wireless/Wired
Dimension	384mm × 460mm × 15mm
Weight	3.0 kg
Water Proof	IP56
Drop Height	70cm
Static Loading	300kg Uniformly
Battery Capacity	8.5 h
Battery Charging	4h in Charger

3. Image Performance

	Typ	Min.
Maximum Linear Dose(uGy)	100uGy	80uGy
MTF @ 0 LP/mm(@RQA5)	1	1
MTF @ 0.5 LP/mm(@RQA5)	87.6%	85.5%
MTF @ 1.0 LP/mm(@RQA5)	70%	65%

	iRay 奕瑞	Doc ID	042-501-01
		Version	A7
	Mars1417X Product Specification	Revision Date	2022-08-11
		Page	3 / 4

MTF @ 1.5 LP/mm(@RQA5)	53.7%	46.9%
MTF @ 2.0 LP/mm(@RQA5)	40.4%	35%
MTF @ 2.5 LP/mm(@RQA5)	30.4%	23.2%
MTF @ 3.0 LP/mm(@RQA5)	22.8%	19%
MTF @ 3.5 LP/mm(@RQA5)	17.3%	11.5%
MTF @ 4.0 LP/mm(@RQA5)	13.5%	10%
MTF @ 4.5 LP/mm(@RQA5)	10.5%	7.3
MTF @ Nyquist(@RQA5)	8.2%	6%
DQE @ 0 LP/mm($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	73.4%	68%
DQE @ 0.5 LP/mm($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	65.8%	58.7%
DQE @ 1.0 LP/mm ($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	55.9%	54%
DQE @ 1.5 LP/mm($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	47.5%	43.4%
DQE @ 2.0 LP/mm ($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	40.4%	38%
DQE @ 2.5 LP/mm($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	34.3%	29.7%
DQE @ 3.0 LP/mm ($2.5 \pm 0.5\mu\text{Gy}/1\mu\text{Gy}$ @RQA5)	28%	25%
DQE @ 3.5 LP/mm($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	22.4%	16%
DQE @ 4.0 LP/mm ($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	17.3%	14%
DQE @ 4.5 LP/mm($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	12.6%	8.1%
DQE @ Nyquist($2.5 \pm 0.5\mu\text{Gy}$ @RQA5)	8.1%	6%

4. Workflow

Trigger Mode	AED (Optional) /Software
Pre-image Time	$\leq 1\text{s}$
Full Image Time	$\leq 3\text{s}$
Cycle Time	$\leq 6\text{s}$

5. Environmental Requirement

Operating Temperature	10°C~35°C
Storage & Transport Temperature with Package	-20°C~55°C
Operating Humidity	5%~90%
Storage & Transport Humidity with Package	5%~95%
Operating Atmospheric Pressure	700mbar~1060mbar
Storage & Transport Atmospheric Pressure	700mbar~1060mbar

	iRay 奕瑞	Doc ID	042-501-01
		Version	A7
	Mars1417X Product Specification	Revision Date	2022-08-11
		Page	4 / 4

6. Detector Reference Drawing




Fig1. Detector Mechanical Outline (unit:mm)