1 1 2010



Binocular brightfield microscope, 1000x, IOS N-PLAN objectives

<b>Observation Method -</b>	Brightfield	Yes
Transmitted Light	Darkfield	As optional
_	Simple polarized light	As optional
	Cimple polarized light	no optional
Main Body	Туре	Upright
	Construction material	Aluminum die-cast
	Trasportation handle	Yes
	·	
Head	Туре	Binocular (Siedentopf)
	Inclination	30°
	360° rotating	Yes
	Interpupillary distance (mm)	48-75
	Dioptric adjustement	On left tube
	Fixing screw for eyepieces	Yes
	Tube inner diameter (mm)	23
Eyepieces	Field number (mm)	20
	Magnification	10x
	Pointer	As optional
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	21
	High eyepoint (for glass wearers)	Yes
	Rubber cup	Yes
Nosepiece	Positions	Quadruple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
		·
Objectives	Optical system	∞
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	40x-1000x
	Туре	IOS N-PLAN
	Objectives included	4x/0.10, W.D. 16.8 mm
		10x/0.25, W.D. 5.8 mm
		40x/0.65, W.D. 0.43 mm
		100x/1.25 (Oil/Water), W.D. 0.13 mm
Stage	Туре	Double layer
	Dimensions (mm)	150x139
	Moving mechanism	Rackless
	Moving range (mm)	75x33
	Material	Anti-scratch painting
	Specimen holder	Yes
	Slide number	1
	X-Y Vernier scale	Yes
	Vernier scale accuracy (mm)	0.1

Candanaar Cinala	T	ALL
Condenser - Single Position	Туре	Abbe
	Removable	Yes
	Numerical aperture (N.A.)	1.25
	Magnification scale for simplified positioning	Yes
	Diaphragms	Iris
	Centrable	Yes
	Focusable	By rack and pinion
F	[ <del>-</del>	
Focusing System	Туре	Coaxial coarse & fine
	Coarse total travel (mm)	18
	Fine total travel (per single rotation) (mm)	0.4
	Fine graduations	100
	Fine resolution (µm)	4
	Upper stop to prevent contact	Yes
	Adjustable tension	Yes
Transmitted Illumination	Kohler illumination	Fixed
	Туре	X-LED
	X-LED type	X-LED3
	Light source power (W)	3.6
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	6
Power Supply for	Туре	External
Transmitted	Microscope connector	Jack, 2.1 mm
Illumination	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	6 Vdc 2.5 A
Accessories Included	Dust cover	Yes
	Immersion oil (10ml)	Yes
	Tension adjustment tool	Yes
	User Manual	Digital version (downloadable)
		<b>5 </b> ( ,
<b>Additional Information</b>		Mirror for transmitted light (as optional).
		External rechargeable battery pack (as optional).
<b>Product Dimensions</b>	Height (mm)	440
	Width (mm)	235
	Depth (mm)	320
<b>Product Weight</b>	(kg)	6.5
-	[· · ·	