


## Ureter Catheter

### To inject contrast liquid

With stylet  
Made of PEBAX  
Tecoflex® USA



#### Straight tip open

Art. No.	Size (Fr/CH)	Length (cm)
<b>UC-O-3</b>	3	70
<b>UC-O-4</b>	4	70
<b>UC-O-5</b>	5	70
<b>UC-O-6</b>	6	70
<b>UC-O-7</b>	7	70

#### Straight tip closed


Art. No.	Size (Fr/CH)	Length (cm)
<b>UC-R-3</b>	3	70
<b>UC-R-4</b>	4	70
<b>UC-R-5</b>	5	70
<b>UC-R-6</b>	6	70
<b>UC-R-7</b>	7	70

Class IIa device - for single use only

## Ureter Catheter

### To inject contrast liquid

With stylet  
Made of PEBAX  
Tecoflex® USA



#### Angled tip open (Tiemann)

Art. No.	Size (Fr/CH)	Length (cm)
<b>UC-AO-3</b>	3	70
<b>UC-AO-4</b>	4	70
<b>UC-AO-5</b>	5	70
<b>UC-AO-6</b>	6	70
<b>UC-AO-7</b>	7	70

#### Angled tip closed (Tiemann)

Art. No.	Size (Fr/CH)	Length (cm)
<b>UC-AR-3</b>	3	70
<b>UC-AR-4</b>	4	70
<b>UC-AR-5</b>	5	70
<b>UC-AR-6</b>	6	70
<b>UC-AR-7</b>	7	70

#### Cone tip open

Art. No.	Shaft (Fr/CH)	Cone (Fr/CH)	Length (cm)
<b>UCC-5/8</b>	5	8	70
<b>UCC-6/10</b>	6	10	70
<b>UCC-7/12</b>	7	12	70

Class IIa device - for single use only