

# **iScope**®

# **HIGHLIGHTS**

- Medical device class I EU MDR 2017-745
- · Provided with APL (Anti-bacterial Protection Layer)
- EWF 10x/22 mm and EWF 10x/20 mm eyepieces
- · Binocular and trinocular models
- · Multihead and face-to-face dual head systems
- · Optional tilting head
- · Quintuple reversed nosepiece
- · Plan, phase and darkfield illumination
- 187/230 x 140 mm rackless stage
- 3 W NeoLED™ Köhler illumination
- · iCare sensor for energy saving
- · 10 years warranty

# SPECIFICATIONS

#### **EYEPIECES**

- Extended plan wide field EWF 10x/20 mm eyepieces with 20 mm field of view and adjustable diopter on the left eyepiece for finity corrected systems (Ø 23.2 mm tube)
- Extended plan wide field EWF 10x/22 mm eyepieces with 22 mm field of view and adjustable diopter on both eyepieces for infinity corrected IOS plan and plan phase systems and adjustable diopter on the left tube for EPLi systems (Ø 30 mm tube)

#### HEAD

- Binocular and trinocular Siedentopf type heads with 30° inclined tubes.
   Interpupillary distance from 48 to 76 mm.
- The trinocular head of the Plan infinity corrected models (IS.1153-PLi) has an optical path selector (100:0 / 50:50) and  $\pm$  5 diopter adjustments on both Ø 30 mm tubes
- The trinocular head of the E-Plan infinity corrected models (IS.1153-EPLi) has a fixed built-in beamsplitter (50:50) and  $\pm$  5 diopter adjustment on the Ø 30 mm left tube
- The trinocular head of the E-plan finite models (IS.1153-EPL) has a fixed built-in 50:50 beamsplitter and one  $\pm$  5 diopter adjustment on the Ø 23.2 mm left tube
- A unique rotating system allows the ergonomic positioning of both tubes in a high (431 mm) and in a low position (397 mm)
- The trinocular head comes with a Ø 23.2 mm photo port

#### **ERGONOMIC TILTING HEAD**

Optional ergonomic 5 to 35° tilting head supplied with EWF 10x/22 mm eyepieces, interpupillary distance 48-75 mm and optional photo attachment with standard Ø 23.2 mm tube (only infinity corrected models)

To order an iScope® with tilting head use reference IS.1158-xxx

To order an iScope® with tilting head and photo tube attachment use reference IS.1159-xxx



IS.1152-PLi

408 (h) x 210 (w) x 255 (d) mm | 9.0 kg

#### **FACE-TO-FACE HEADS**

- The iScope® can be supplied with two heads in a face-to-face configuration allowing simultaneous observation by two operators
- The 30 mm diameter tubes of the head are equipped with EWF 10x/20 mm evenieces
- The main binocular head has one diopter adjustment, the second head has two adjustments
- Only available for the model with plan infinity corrected objectives (IS 1154-PI i)
- The face-to-face head is equipped with a 2-color laser pointer

### **MULTIHEAD SYSTEM**

- The iScope® can be extended with a unique multihead system for in total two, three or five heads, allowing simultaneous observation of specimens.
- The central attachment is equipped with a joystick to move a green and red laser pointer across the entire field of view of all heads
- Configurations with one, two or four additional viewing binocular heads, 30° inclined tubes and plan 4x, 10x, S40x, S100x oil immersion infinity corrected IOS objectives
- Each extra viewing binocular head is equipped with extended wide field plan EWF 10x/22 mm eyepieces

(references: IS.1156-PLi-x, x = total number of heads)



#### **OBJECTIVES**

| E-Plan EPL           | 4x/0.10 | 10x/0.25 | 20x/0.40 <sup>(1)</sup> | S40x/0.65 |                          | S100x/1.25 oil |
|----------------------|---------|----------|-------------------------|-----------|--------------------------|----------------|
| E-Plan EPLi IOS      | 4x/0.10 | 10x/0.25 | 20x/0.40 <sup>(1)</sup> | S40x/0.65 |                          | S100x/1.25 oil |
| Plan PLi IOS         | 4x/0.10 | 10x/0.25 | 20x/0.40 <sup>(1)</sup> | S40x/0.65 | S60x/0.85 <sup>(1)</sup> | S100x/1.25 oil |
| Plan phase PLPH      |         | 10x/0.25 | 20x/0.40                | S40x/0.65 |                          | S100x/1.25 oil |
| Plan phase PLPHi IOS |         | 10x/0.25 | 20x/0.40                | S40x/0.65 |                          | S100x/1.25 oil |

<sup>(1)</sup> optional

All optics are anti-fungus treated and anti-reflection coated for maximum light throughput

#### **NOSEPIECE**

Revolving quintuple reversed nosepiece for max. five objectives

#### STAGE

The iScope® can be equipped with three types of stages (designed for 2 slides):

- 156 x 138 mm stage equipped with integrated 79 x 52 mm X-Y mechanical stage
- 187/230 x 140 mm rackless stage equipped with double slide holder and integrated 79 x 52 mm X-Y mechanical stage. The iScope® rackless stage has no protruding parts, enables more smooth movements and is safer
- 220 x 157 mm ceramic stage with integrated 75 x 50 mm X-Y mechanical stage. The ceramic coating protects the stage effectively against marks and scratches. The surface also ensures stray light not to be reflected from the stage into the objective

The iScope® can be supplied with a heating stage which can be set up to 50° Celsius by a PID temperature controller. Only available with newly purchased microscopes. Higher temperatures can be achieved on special request

#### CONDENSERS WITH PHASE CONTRAST SLIDER

There is a choice of two optional NA. 1.25 phase contrast condenser sets with phase contrast sliders and plan phase contrast objectives. The first version one is comes with plan phase 10x and S40x objectives with matching slider, the second version comes with plan phase 20x and and S100x oil immersion objectives. Available for iScope 160mm and IOS infinity versions All sets are supplied with centering telescope and green opaque filter

# CONDENSER FOR BRIGHTFIELD

The standard height adjustable Abbe N.A. 1.25 condenser for brightfield accepts sliders with phase annuli suitable for plan phase 10x/20x or S40x/S100x oil immersion IOS objectives for economical phase contrast. With magnification indication. A slider with a simple dark stop for darkfield up to 400x magnification is also available

### CONDENSER FOR ZERNIKE PHASE CONTRAST

An optional height adjustable Zernike NA. 1.25 phase contrast disc condenser with plan phase 10/20/S40x and S100x oil immersion objectives and darkfield stop position for darkfield contrast up to 400x magnification. Supplied with alignment telescope and green filter

#### **CONDENSER FOR DARKFIELD**


A state-of-the-art condenser equipped with reflective cardioid mirrors, a high powered 5 W LED and a S100x objective with built-in iris diaphragm enable a real 1000x magnification darkfield solution.


#### **FOCUSING**

Coaxial coarse and fine adjustments, 200 graduations, 1  $\mu$ m per graduation, 200  $\mu$ m per rotation, total travel range is approximately 24 mm. Supplied with an adjustable rack stop to prevent damage to sample and objectives. The coarse adjustments are equipped with friction control

#### ILLUMINATION

- 3 W adjustable Köhler NeoLED™ diascopic illumination with internal 100-240 V power supply
- The innovative NeoLED™ design offers larger apertures, allowing the optical system of the iScope® microscope to produce images at higher resolutions, very close to the theoretical diffraction limit of the optics.
   Other benefits of the NeoLED™ is the low energy consumption, no heating and a long operating life span
- The Köhler illumination on models with IOS plan and plan phase infinity corrected system provides high contrast and a maximum achievable resolving power of the optics. Also available for other models as option





Normal LED

NeoLED™

#### **ICARE SENSOR**

The unique iCare Sensor is developed to avoid unnecessary loss of energy. The illumination of the microscope automatically switches off shortly after microscopists step away from their position

### CSS - CABLE STORAGE SYSTEM

- iScope® allows users to easily insert the power cable into the back of the instrument, which enables easy storage
- The integrated carrying grip at the back of the microscope ensures safe transportation of the microscope

#### **PACKAGE CONTENT**

- Supplied with power cord, dust cover, a spare fuse, user manual and 5 ml immersion oil for models with S100x objective
- $\bullet \ \ \, \text{Phase contrast models are supplied with green filter and alignment telescope}$
- All packed in polystyrene boxes



# ISCOPE® FOR LIFE SCIENCE

(Medical device class I)

|               |   | Trino | Phase<br>contrast | EWF<br>10x22<br>mm | EWF<br>10x20<br>mm | E-plan 4x/10x/<br>40x/100x<br>objectives | Plan phase<br>10x/20x/40x/<br>100x objectives | E-plan IOS<br>4x/10x/ 40x/<br>100x objectives | Plan IOS<br>4x/10x/ 40x/<br>100x objectives | Plan phase IOS<br>10x/20x/40x/<br>100x objectives | Mechanical<br>rackless<br>stage | iCare<br>Sensor | Köhler<br>LED |
|---------------|---|-------|-------------------|--------------------|--------------------|--|---|---|---|---|---------------------------------|-----------------|---------------|
| IS.1152-EPL   | • |       |                   |                    | •                  | •  |   |   |   |   | •                               | •               |               |
| IS.1153-EPL   |   | •     |                   |                    | •                  | •  |   |   |   |   | •                               | •               |               |
| IS.1152-PLPH  |   |       | •                 |                    | •                  |  | •   |   |   |   | •                               | •               |               |
| IS.1153-PLPH  |   | •     | •                 |                    | •                  |  | •   |   |   |   | •                               | •               |               |
| IS.1152-EPLi  | • |       |                   | •                  |                    |  |   | •   |   |   | •                               | •               |               |
| IS.1153-EPLi  |   | •     |                   |                    |                    |  |   | •   |   |   | •                               | •               |               |
| IS.1152-PLi   | • |       |                   | • (1)              |                    |  |   |   | •   |   | •                               | •               |               |
| IS.1153-PLi   |   | •     |                   | • (1)              |                    |  |   |   | •   |   | •                               | •               | •             |
| IS.1152-PLPHi |   |       | •                 | • (1)              |                    |  |   |   |   | •   | •                               |                 |               |
| IS.1153-PLPHi |   | •     | •                 | • (1)              |                    |  |   |   |   | •   | •                               | •               | •             |

<sup>(1)</sup> Two tubes with diopter adjustments

# ISCOPE® FOR LIFE SCIENCE (INFINITY - ERGONOMIC TILTING HEAD)

(Medical device class I)

| MODELS        | Bino | Photo attachment | Phase contrast | EWF<br>10x22 mm | E-plan IOS 4x/10x/<br>40x/100x objectives | Plan IOS 4x/10x/<br>40x/100x objectives | Plan phase IOS 10x/20x/<br>40x/100x objectives | Mechanical rackless stage | iCare Sensor | Köhler<br>LED |
|---------------|------|------------------|----------------|-----------------|---|---|--|---------------------------|--------------|---------------|
| IS.1158-EPLi  |      |                  |                | •               | •   |   |  | •                         | •            |               |
| IS.1159-EPLi  |      | •                |                | •               | •   |   |  | •                         | •            |               |
| IS.1158-PLi   |      |                  |                | •               |   | •                                       |  | •                         | •            | •             |
| IS.1159-PLi   |      | •                |                | •               |   | •                                       |  | •                         | •            | •             |
| IS.1158-PLPHi | •    |                  | •              | •               |   |   | •  | •                         | •            | •             |
| IS.1159-PLPHi |      | •                | •              | •               |   |   | •  | •                         | •            |               |

#### ISCOPE® FOR LIFE SCIENCE WITH SMART LIGHT CONTROL (SLC) - (INFINITY MODELS)

(Medical device class I)

| MODELS           | Bino | Trino | EWF 10x22 mm | E-plan IOS 4x/10x/<br>40x/100x objectives | Plan IOS 4x/10x/ 40x/100x<br>objectives | Mechanical<br>rackless stage | iCare Sensor | Köhler LED |
|------------------|------|-------|--------------|---|---|------------------------------|--------------|------------|
| IS.1152-EPLi/SLC | •    |       | •            | •   |   | •                            | •            |            |
| IS.1153-EPLi/SLC |      | •     | •            | •   |   | •                            | •            |            |
| IS.1152-PLi/SLC  | •    |       | •*           |   | •                                       | •                            | •            | •          |
| IS.1153-PLi/SLC  |      | •     | •*           |   | •                                       | •                            |              |            |

# ISCOPE® FOR LIFE SCIENCE (MULTIHEAD SYSTEMS)

(Medical device class I)

| MODELS       | Total users | Binocular | Trinocular | EWF 10x22 mm | Plan IOS 4x/10x/<br>40x/100x objectives | Mechanical rackless stage | iCare sensor | Köhler LED |
|--------------|-------------|-----------|------------|--------------|---|---------------------------|--------------|------------|
| IS.1156-PLi2 | 2           | 1x        | •          | •            | •                                       | •                         | •            | •          |
| IS.1156-PLi3 | 3           | 2x        | •          | •            | •                                       | •                         |              | •          |
| IS.1156-PLi5 | 5           | 4x        | •          | •            | •                                       | •                         | •            | •          |
| IS.1156-PLi9 | 9           | 8x        | •          |              | •                                       | •                         | •            |            |

# ISCOPE® FOR LIFE SCIENCE (FACE-TO-FACE DUAL HEAD SYSTEM)

(Medical device class I)

| MODELS         | Total users | Binocular<br>EWF 10x/20 mm | Trinocular EWF<br>10x/20 mm | E-Plan IOS 4x/10x/<br>40x/100x objectives | Plan IOS 4x/10x/<br>40x/100x objectives | Mechanical rackless stage | iCare sensor | Köhler LED |
|----------------|-------------|----------------------------|-----------------------------|---|---|---------------------------|--------------|------------|
| IS.1154-PLi    | 2           | 2x                         |                             |   | •                                       | •                         | •            | •          |
| IS.1154-EPLi   | 2           | 2x                         |                             | •   |   | •                         | •            |            |
| IS.1154-PLi/T  | 2           | 1x                         | 1x                          |   | •                                       | •                         | •            | •          |
| IS.1154-EPLi/T | 2           | 1x                         | 1x                          | •   |   | •                         | •            |            |


# ISCOPE® FOR LIFE SCIENCE (DARKFIELD CONTRAST APPLICATION)

| MODELS          | Trino | Darkfield | EWF 10x20 mm | EWF 10x22 mm | E-plan 4x/10x/<br>40x/100x objectives* | Plan IOS 4x/10x/ 40x/100x<br>objectives* | Mechanical rackless stage | iCare sensor | Köhler LED |
|-----------------|-------|-----------|--------------|--------------|--|--|---------------------------|--------------|------------|
| IS.1153-PLi/DF  |       | •         |              | •            |  | •  | •                         | •            |            |
| IS.1153-PLi/DFi |       | •         |              | •            |  | •  | •                         | •            | •          |
| IS.1153-EPL/DF  |       |           | •            |              | •                                      |  |                           | •            |            |

<sup>\*</sup> Models for darkfield observation IS.1152-PLi/DF and IS.1153-PLi/DF are supplied with a state-of-the-art condenser equipped with reflective cardioid mirrors and a high powered 5 W LED. Together with a S100x objective with built-in iris diaphragm real 1000x magnification darkfield solution can be achieved. All other specifications are identical to models IS.1152-PLi and IS.1153-PLi. By adding the IS.9150 (darkfield cardioid mirror condenser with external 100-240 V power supply) and the 86.521 (S100x objective with built-in iris diaphragm) or the IS.7200-I (super contrast S100x infinity corrected IOS objective), an existing iScope brightfield microscope can be upgraded to darkfield as well

**ISCOPE** | 3/6









# APL (ANTI-BACTERIAL PROTECTION LAYER)

APL is a revolutionary paint treatment applied to the most critical parts of our products. A microscope with APL will restrict the growth of micro-organisms, including bacteria and mold

# ACCESSORIES AND SPARE PARTS

Pair of eyecups infinity models (Ø30 mm tube)

# EYEPIECES (23.2 MM)

| ETEPTEC    | .E3 (23.2 IVIIVI)                                       |           |  |
|------------|---|-----------|--|
| IS.6010    | EWF 10x/20 mm eyepiece (Ø23.2 mm tube)                  | IS.7202   | Plan PLi 2x/0.05 IOS objective, WD 18.3 mm. Best to be used        |
| IS.6010-P  | EWF 10x/20 mm eyepiece with pointer (Ø23.2 mm tube)     |           | together with swing-out condenser                                  |
| IS.6010-C  | EWF 10x/20 mm eyepiece with crosshair (Ø23.2 mm tube)   | IS.7204   | Plan PLi 4x/0.10 IOS objective. WD 15.4 mm                         |
| IS.6010-CN | EWF 10x/20 mm eyepiece with 10/100 micrometer and cross | IS.7210   | Plan PLi 10x/0.25 IOS objective. WD 10 mm                          |
|            | (Ø23.2 mm tube)   | IS.7220   | Plan PLi 20x/0.40 IOS objective. WD 5.1 mm                         |
| IS.6015    | WF 15x/16 mm eyepiece (Ø23.2 mm tube)                   | IS.7240   | Plan PLi S40x/0.65 IOS objective. WD 0.54 mm                       |
| IS.6020    | WF 20x/12 mm eyepiece (Ø23.2 mm tube)                   | IS.7260   | Plan PLi S60x/0.85 IOS objective. WD 0.14 mm                       |
| IS.6099    | Pair of eyecups, Ø 23.2 mm tube                         | IS.7200   | Plan PLi S100x/1.25 oil IOS objective. WD 0.13 mm                  |
|            |   | IS.7200-I | Plan Super Contrast PLi S100x/1.25 oil IOS objective with built-in |
| EYEPIEC    | ES (30 MM)  |           | iris diaphragm. WD 0.13 mm   |
| IS.6210    | EWF 10x/22 mm eyepiece (Ø 30mm tube)                    |           |  |
| IS.6210-C  | EWF 10x/22 mm eyepiece with crosshairs (Ø30 mm tube)    | IS.8910   | Plan PLPHi 10x/0.25 phase contrast IOS infinity corrected          |
| IS.6210-P  | EWF 10x/22 mm eyepiece with pointer (Ø30 mm tube)       |           | objective. WD 10.2 mm  |
| IS.6210-CM | EWF 10x/22 mm eyepiece with 10/100 micrometer and       | IS.8920   | Plan PLPHi 20x/0.40 phase contrast IOS infinity corrected          |

|            |   | 13.7200-1 | Fight Super Contrast FEI 3100X/1.23 on 103 objective with built-i |
|------------|---|-----------|---|
| EYEPIEC    | ES (30 MM)  |           | iris diaphragm. WD 0.13 mm  |
| IS.6210    | EWF 10x/22 mm eyepiece (Ø 30mm tube)                        |           |   |
| IS.6210-C  | EWF 10x/22 mm eyepiece with crosshairs (Ø30 mm tube)        | IS.8910   | Plan PLPHi 10x/0.25 phase contrast IOS infinity corrected         |
| IS.6210-P  | EWF 10x/22 mm eyepiece with pointer (Ø30 mm tube)           |           | objective. WD 10.2 mm   |
| IS.6210-CM | EWF 10x/22 mm eyepiece with 10/100 micrometer and           | IS.8920   | Plan PLPHi 20x/0.40 phase contrast IOS infinity corrected         |
|            | crosshairs (Ø30 mm tube)                                    |           | objective. WD 5.1 mm  |
| IS.6212    | WF 12.5x/17 mm eyepiece (Ø30 mm tube)                       | IS.8940   | Plan PLPHi S40x/0.65 phase contrast IOS infinity corrected        |
| IS.6212-W  | WF 12.5x/17 mm eyepiece with Walton Beckett reticle         |           | objective. WD 0.5 mm  |
|            | (Ø30 mm tube)   | IS.8900   | Plan PLPHi S100x/1.25 oil phase contrast IOS infinity corrected   |
| IS.6215    | WF 15x/16 mm eyepiece (Ø30 mm tube)                         |           | objective. WD 0.13 mm   |
| IS.6215-CM | WF 15x/16 mm eyepiece with 10/100 micrometer and crosshairs |           |   |
|            | (Ø 30 mm tube)  | CONDE     | NSERS   |
| IS.6220    | WF 20x/12 mm eyepiece (Ø30 mm tube)                         | IS.9102   | Standard Abbe condenser 1.25 NA with slot for darkfield and       |
|            |   |           |   |

phase contrast sliders

Swing-out 0.9/1.25 N.A. condenser

IS.6299

| OBJEC   | TIVES   | IS.9150 | Cardiod darkfield condenser with integrated 5 W LED light        |
|---------|---|---------|--|
| IS.7104 | E-plan EPL 4x/0.10 objective. WD 15.2 mm                      |         | source and external 100-240 V mains adapter                      |
| IS.7110 | E-plan EPL 10x/0.25 objective. WD 5.5 mm                      | 86.521  | Plan PL S100x/1.25 oil immersion objective with built-in iris    |
| IS.7120 | E-plan EPL 20x/0.40 objective. WD 3.5 mm                      |         | diaphragm. WD 0.33 mm  |
| IS.7140 | E-plan EPL S40x/0.65 objective. WD 0.45 mm                    |         |  |
| IS.7160 | E-plan EPL S60x/0.85 objective. WD 0.19 mm                    | PHASE   | CONTRAST ATTACHMENTS   |
| IS.7100 | E-plan EPL S100x/1.25 oil objective. WD 0.13 mm               | IS.9124 | Zernike phase contrast set including rotating disc with PLPH     |
|         |   |         | 10/20/40/100, brightfield and darkfield position                 |
| IS.7710 | Plan PLPH 10x/0.25 phase contrast objective. WD 12.2 mm       | IS.9127 | Zernike phase contrast set including rotating disc with PLPH     |
| IS.7720 | Plan PLPH 20x/0.40 phase contrast objective. WD 5 mm          |         | 10/20/40/100, brightfield and darkfield position                 |
| IS.7740 | Plan PLPH S40x/0.65 phase contrast objective. WD 0.37 mm      | IS.9148 | Alignment telescope for phase contrast diameter 30mm tube        |
| IS.7700 | Plan PLPH S100x/1.25 oil phase contrast objective. WD 0.13 mm | IS.9149 | Alignment telescope for phase contrast diameter 23.2mm tube      |
|         |   | IS.9160 | Phase contrast slider set with 10x and S40x PLPH objectives and  |
| IS.8804 | E-plan EPLi 4x/0.10 IOS objective. WD 15.4 mm                 |         | annuli for 10/S40x PLPH objectives. Also suitable for optional   |
| IS.8810 | E-plan EPLi 10x/0.25 IOS objective. WD 5.8 mm                 |         | 20x PLPH objective   |
| IS.8840 | E-plan EPLi S40x/0.65 IOS objective. WD 0.43 mm               | IS.9161 | Phase contrast slider set with 20x and S100x PLPH objectives and |
| IS.8800 | E-plan EPLi S100x/1.25 oil IOS objective . WD 0.13 mm         |         | annuli for 20x/S100x PLPH objectives                             |

IS.9105

ISCOPE | 5/6



| IS.9162 | Phase contrast slider set with 10x and S40x PLPHi IOS infinity    |
|---------|---|
|         | corrected objectives and annuli for 10x/S40x PLPHi IOS infinity   |
|         | corrected objectives.   |
|         | Also suitable for optional 20x PLPHi infinity corrected objective |
| IS.9163 | Phase contrast slider set with 20x and S100x PLPHi IOS infinity   |
|         | corrected objectives and annuli for 20x/S100x PLPHi IOS infinity  |
|         | corrected objectivest   |
| IS.9194 | Slider with phase contrast annuli for S40x phase contrast         |
|         | objective   |
|         |   |

# **POLARIZATION ATTACHMENTS**

| IS.9600 | Polarization filter 45 mm for lamphouse                           |
|---------|---|
| IS.9601 | Polarization set: simple rotating polarizer for lamphouse and fix |
|         | polarizer mounted under head                                      |
| IS.9626 | Polarization filter for mounting under the head                   |

# **FILTERS**

| IS.9600 | Polarization filter 45 mm for lamphouse                                     |
|---------|---|
| IS.9601 | $Polarization \ set: simple \ rotating \ polarizer \ for \ lamphouse \ and$ |
|         | fixed polarizer mounted under head  |
| IS.9626 | Polarization filter for mounting under the head                             |
| IS.9700 | Blue filter 45 mm for lamphouse   |
| IS.9702 | Green filter 45 mm for lamphouse  |
| IS.9704 | Yellow filter 45 mm for lamphouse   |
| IS.9706 | White opaque filter 45 mm for lamphouse                                     |
|         |   |

# **CAMERA ACCESSORIES**

| IS.9800 | Single photo tube attachment with one 23.2 mm tube for           |
|---------|--|
|         | IS.5700 ergonomic tilting head of iScope® infinity systems       |
| AE.5130 | Universal SLR adapter with built-in 2x lens for standard 23.2 mm |
|         | tube. Needs T2 adapter   |
| AE.5025 | T2 ring for Nikon D SLR digital camera                           |
| AE.5040 | T2 ring for Canon EOS SLR digital camera                         |

# **MISCELLANEOUS**

Slider with darkfield stop

IS.9170

IS.9194

|           | objective   |
|-----------|---|
| IS.9503   | Large ceramic stage. Only with new microscopes, add /C suffix   |
|           | after iScope® model part number                                 |
| IS.9880   | Köhler attachment   |
| IS.4300   | Aluminum transport case for iScope                              |
| AE.9916   | Euromex dust cover extra large (50 x 68 cm)                     |
| AE.9919   | Nylon microscope bag (58 x 32 x 24 cm)                          |
| AE.3684   | Glass fuses 500 mA 250 V, 10 pieces                             |
| AE.5168-I | Heating stage series with controller, only with new microscopes |
| SL.5500   | NeoLED™ replacement unit  |
| IS.9993   | NeoLED replacement unit for iScope                              |
|           |   |

Microscope slides 76 x 26 mm, ground edges, 50 pieces per pack

Slider with phase contrast annuli for S40x phase contrast

#### **DISPOSABLES**

PB.5155

|           | white color, 50 pieces per pack  |
|-----------|--|
| PB.5157-B | Microscope slides 76 x 26 mm, ground edges and frosted side            |
|           | blue color, 50 pieces per pack   |
| PB.5165   | Cover glasses 18 x 18 mm, 0.13-0.17 mm, 100 pieces                     |
| PB.5168   | Cover glasses 22 x 22 mm, 0.13-0.17 mm, 100 pieces                     |
| PB.5245   | Lens cleaning paper, 100 sheets per pack                               |
| PB.5255   | Immersion oil, 25 ml. Refraction index n = 1.482                       |
| PB.5274   | lso propyl alcohol 99%, 200 ml   |
| PB.5275   | Cleaning kit: lens fluid, lint free lens tissue/paper, brush, air      |
|           | blower, cotton swabs   |
| PB.5276   | Microscope maintenance and servicing kit, 16pcs: cleaning              |
|           | brush, 6 pcs screwdriver set, air blower, 3 pcs Allen key, 1.5, 2, 2.5 |
|           | mm, lens cleaning fluid 20 ml, cleaning cloth 140 x 140 mm, 100 $$     |
|           | pcs Lens tissue sheets, Tube of maintenance grease, 10 ml bottle       |

of oil, packed in a nice toolbox

**PB.5157-W** Microscope slides 76 x 26 mm, ground edges and frosted side

WD = working distance







• AE.9919





