



NOTES

1. Assembly as shown. No components missing or not as described on the bill of materials.
2. Embedded particles should not be larger than 0.4mm, and no more than 3 spots for each part.
3. Gate or parting line should not be larger than 0.4mm.
4. Flashes should not be larger than 0.4mm.
5. The bonding strength of all connections should not be less than 15N/15seconds.
6. Other physical, chemical and biological properties should be in accordance with ISO8536-8 and ISO8536-4.

12	/	Protective cap	1	
11	/	Male luer Lock	1	
10	/	PVC free tube 150mm	1	OD:4.1 ± 0.07mm ID:3 ± 0.07mm
9	/	0.2 micron filter	1	
8	/	Roller clamp	1	
7	/	PVC free tube 2350mm	1	OD:4.1 ± 0.07mm ID:3 ± 0.07mm
6	/	Solution filter 15um	1	
5	/	20drops/ml Drop chamber	1	
4	/	Vent spike	1	
3	/	Air filter	1	
2	/	Air Inlet closure	1	
1	/	Protective cap	1	
Items	Part NO.	Part Name	QTY	Remark
Discription	Disposable infusion set (A35001CI)		Part No.	A35001CI
Draw/Date	Simon/2017. 4. 1	Material	/	Model
			A021M02	Revision
				V1.0