

**All models accept wire 0.035"**

Tous les modèles acceptent des fils guides de 0,035" / Todos los modelos aceptan guía de 0,035"

### Broncho Dilation Balloons

/Indications bronchiques /Para procedimientos bronquiales



Reference Réf. / Ref.	CATHETER CATHÉTER / CATÉTER		Length (mm) Long. / Longitud	BALLOON BALLON / BALÓN	
	Length (cm) Long. / Longitud	Diam. (mm) Diam. / Diám.		Diam. (mm/Fr) Diam. / Diám.	Nominal Pressure (atm/psi) Pression nominale / Presión nominal
EZM1030P-120	120	2.3	30	10-11-12 30-33-36	3-5-7 45-75-105
EZM1230P-120	120	2.3	30	12-13.5-15 36-40.5-45	3-5-7 45-75-105
EZM1055-120	120	2.3	55	10-11-12 30-33-36	3-5-7 45-75-105
EZM1255-120	120	2.3	55	12-13.5-15 36-40.5-45	3-4.5-7.5 45-67.5-112.5
EZM1555-120	120	2.3	55	15-16.5-18 45-49.5-54	3-4.5-6.5 45-67.5-97.5
EZM1855-120	120	2.3	55	18-19-20 54-57-60	3-4.5-5.5 45-67.5-82.5

### For Esophageal and Colonic procedures

/Indications oesophagiennes, duodénales et coliques /Para procedimientos esofágicos y colónicos



Reference Réf. / Ref.	CATHETER CATHÉTER / CATÉTER		Length (mm) Long. / Longitud	BALLOON BALLON / BALÓN	
	Length (cm) Long. / Longitud	Diam. (mm) Diam. / Diám.		Diam. (mm/Fr) Diam. / Diám.	Nominal Pressure (atm/psi) Pression nominale / Presión nominal
EZM0655	240	2.3	55	6-7-8 18-21-24	3-6-10 45-90-150
EZM0855	240	2.3	55	8-9-10 24-27-30	3-5.5-8 45-82.5-120
EZM1055	240	2.3	55	10-11-12 30-33-36	3-5-7 45-75-105
EZM1255	240	2.3	55	12-13.5-15 36-40.5-45	3-4.5-7.5 45-67.5-112.5
EZM1555	240	2.3	55	15-16.5-18 45-49.5-54	3-4.5-6.5 45-67.5-97.5
EZM1855	240	2.3	55	18-19-20 54-57-60	3-4.5-5.5 45-67.5-82.5

\*Styler transpassing catheter in 10 cm /Styler dépassant de 10 cm du cathéter /Estilote pasando en 10cm el catéter

### For Pyloric and Biliary procedures

/Indications pyloriques et biliaires /Para procedimientos pilóricos y biliares



Reference Réf. / Ref.	CATHETER CATHÉTER / CATÉTER		Length (mm) Long. / Longitud	BALLOON BALLON / BALÓN	
	Length (cm) Long. / Longitud	Diam. (mm) Diam. / Diám.		Diam. (mm/Fr) Diam. / Diám.	Nominal Pressure (atm/psi) Pression nominale / Presión nominal
EZM0430	240	2.3	30	4/12	6/90
<b>EZM0630P</b>	240	2.3	30	<b>6-7-8</b> 18-21-24	3-6-10 45-90-150
EZM0830P	240	2.3	30	8-9-10 24-27-30	3-5.5-8 45-82.5-120
EZM1030P	240	2.3	30	10-11-12 30-33-36	3-5-7 45-75-105
EZM1230P	240	2.3	30	12-13.5-15 36-40.5-45	3-4.5-7.5 45-67.5-112.5