



AR(K)7610

Auto Refrac(Kera)tometer

The most cost-effective
Hartmann refrac(kera)tometer in the world

Do what you want to do, save what you hope in time and money

Operation interface function

Intuitive icons provide the user an easier operating circumstance, and make the measurement become more convenient and the data to be measured more accurate and fast.

Measurement with glasses frame

The patient with glasses or contact lenses can be directly measured whether it is undercorrected or overcorrected.

Super-high power measurement

Power of 20.00 can be easily and accurately measured.

Up/down Auto Tracking

Adjustable LCD Touch Screen

High brightness and contrast 7" wide color TFT LCD screen, smooth touch mode, different angle can be adjusted.


Motorized Chin Rest

By pressing the Up & Down buttons, the users can set and adjust the height of the patient's chin freely and quickly.

Data Record

3 groups of data stored each measurement, maximum 10 groups of data can be stored.

Hartmann imaging processing technology



Professional Design

