

Add: 307, Block 18, No.644, Shibei Industry Road, Dashi Street, Panyu District, Guangzhou, China Email: <u>info@melison-medical.com</u>

## DOUBLE DOOR AUDIOMETRIC BOOTH-SM1513 Technical Data Sheet

| No. | ltem   | Technical Data   | Unit  | Qty |
|-----|--|--|-------|-----|
| 1   | Audiometric<br>Booth<br>/Soundproof<br>Booth<br>Overview | <ol> <li>General Specifications:         <ol> <li>Double-layer Wall and double door, Steel&amp;Wood modular structure</li> <li>Outer Dimensions: 1.5*1.5*2.3m<br/>Inner Dimensions: 1.3*1.3*2.0m</li> <li>Area: 1.95m<sup>2</sup>;</li> <li>The thickness of the wall is about 200mm.</li> <li>The size of the soundproof booth windowis 380*600MM.</li> <li>With this specification, the cost on space and materials are minimized while the soundproof effect is guaranteed.</li> <li>Electrostatic spraying technology is applied to the exterior wall surface while a polyester fiber sound absorbing panel is used for the interior wall.</li> <li>Implementation Standards:                  <ol></ol></li></ol></li></ol> | Piece | 1   |
| 2   | Main body of<br>the<br>Soundproof<br>Booth               | Fireproof, anti-corrosion, anti-rust, moisture-proof, pest-proof, easy to disinfect, non-toxic, odorless, radiation-free   |       |     |
| 3   | Exterior Wall  | 1.5mm steel plates with spray, detachable and assembled for multiple times; Color: milky white/beige   |       |     |
| 4   | Indoor sound<br>absorption<br>treatment                  | The interior wall is covered by the polyester fiber sound absorbing panels   |       |     |



Add: 307, Block 18, No.644, Shibei Industry Road, Dashi Street, Panyu District, Guangzhou, China Email: <u>info@melison-medical.com</u>

| 5  | Double-layer<br>soundproof<br>Window         | Wedge damping soundproof window made of double-layer perspective glass   | Piece | 1 |
|----|--|--|-------|---|
| 6  | Soundproof<br>Door                           | double-layer magnetically sealed soundproof door: 0.84*1.94m; Long service life door shaft; noise-free design  | Piece | 1 |
| 7  | Ventilation<br>Equipment                     | Inlet Vent, Exhaust Fan  | Set   | 1 |
| 8  | Floor  | Eco-friendly sound-absorbing plastic floor   | Piece | 1 |
| 9  | Signal<br>Transfer<br>Jack and<br>Connection | 6 sets of single and dual channel signal mixing technology to ensure<br>that all devices can be used with one kind of connection, and the wire<br>is made of silver mils, ensuring no signal loss and ensuring the<br>accuracy of the audiometer test results. | Set   | 1 |
| 10 | Interior<br>Lighting                         | Internal silent lighting   | Set   | 1 |
| 11 | Power<br>Socket                              | 2-hole/3-hole Universal Socket   | Set   | 1 |
| 12 | Lighting<br>Switch                           |  | Set   | 1 |
| 13 | Ventilation<br>Switch                        |  | Set   | 1 |
| 14 | Device<br>Hanger                             |  | Set   | 1 |





Add: 307, Block 18, No.644, Shibei Industry Road, Dashi Street, Panyu District, Guangzhou, China Email: <u>info@melison-medical.com</u>

# Sample photos: Double door- Open outside











Add: 307, Block 18, No.644, Shibei Industry Road, Dashi Street, Panyu District, Guangzhou, China Email: <u>info@melison-medical.com</u>

# Double door - open inside & outside







