

EC Declaration of Conformity

according to Annex II of Directive 93/42/EEC concerning medical devices, as amended by Directive 2007/47/EC

Classification according to Directive 2005/50/EC: Class III

We

Waldemar Link GmbH & Co. KG
Barkhausenweg 10
D-22339 Hamburg

declare under our own responsibility that

NON ACTIVE IMPLANTS FOR JOINT REPLACEMENT:

MobileLink[®] ACETABULAR CUP SYSTEM

meet the respective provisions of the Directive 93/42/EEC concerning medical devices, as amended by Directive 2007/47/EC and we are solely responsible for the preparation of this declaration. The relevant technical documentation is archived by the QM department.

The product is marked (CE0482) by MEDCERT Zertifizierungs- und Prüfgesellschaft für die Medizin GmbH Pilatuspool 2, D-20355 Hamburg.

Hamburg, 25.08.2020 
Quality Management

Hamburg, 25.08.2020 
Management Representative

Valid from: 25.08.2020
Valid to: 11.06.2022

Annex 1

Article number and description

MobileLink Acetabular Cup System

PlasmaLink Shell, cluster hole

Article Number	Description
183-110/42	O-Ø 42 mm, I-Ø 36 mm, for Insert Size A
183-110/44	O-Ø 44 mm, I-Ø 36 mm, for Insert Size A
183-110/46	O-Ø 46 mm, I-Ø 40 mm, for Insert Size B
183-110/48	O-Ø 48 mm, I-Ø 40 mm, for Insert Size B
183-110/50	O-Ø 50 mm, I-Ø 44 mm, for Insert Size C
183-110/52	O-Ø 52 mm, I-Ø 44 mm, for Insert Size C
183-110/54	O-Ø 54 mm, I-Ø 48 mm, for Insert Size D
183-110/56	O-Ø 56 mm, I-Ø 48 mm, for Insert Size D
183-110/58	O-Ø 58 mm, I-Ø 52 mm, for Insert Size E
183-110/60	O-Ø 60 mm, I-Ø 52 mm, for Insert Size E
183-110/62	O-Ø 62 mm, I-Ø 54 mm, for Insert Size F
183-110/64	O-Ø 64 mm, I-Ø 54 mm, for Insert Size F
183-110/66	O-Ø 66 mm, I-Ø 54 mm, for Insert Size F
183-110/68	O-Ø 68 mm, I-Ø 54 mm, for Insert Size F
183-110/70	O-Ø 70 mm, I-Ø 54 mm, for Insert Size F
183-110/72	O-Ø 72 mm, I-Ø 54 mm, for Insert Size F

TiCaP Shell, cluster hole

Article Number	Description
183-101/42	O-Ø 42 mm, I-Ø 36 mm, for Insert Size A
183-101/44	O-Ø 44 mm, I-Ø 36 mm, for Insert Size A
183-101/46	O-Ø 46 mm, I-Ø 40 mm, for Insert Size B
183-101/48	O-Ø 48 mm, I-Ø 40 mm, for Insert Size B
183-101/50	O-Ø 50 mm, I-Ø 44 mm, for Insert Size C
183-101/52	O-Ø 52 mm, I-Ø 44 mm, for Insert Size C
183-101/54	O-Ø 54 mm, I-Ø 48 mm, for Insert Size D
183-101/56	O-Ø 56 mm, I-Ø 48 mm, for Insert Size D
183-101/58	O-Ø 58 mm, I-Ø 52 mm, for Insert Size E

183-101/60	O-Ø 60 mm, I-Ø 52 mm, for Insert Size E
183-101/62	O-Ø 62 mm, I-Ø 54 mm, for Insert Size F
183-101/64	O-Ø 64 mm, I-Ø 54 mm, for Insert Size F
183-101/66	O-Ø 66 mm, I-Ø 54 mm, for Insert Size F
183-101/68	O-Ø 68 mm, I-Ø 54 mm, for Insert Size F
183-101/70	O-Ø 70 mm, I-Ø 54 mm, for Insert Size F
183-101/72	O-Ø 72 mm, I-Ø 54 mm, for Insert Size F

TrabecuLink Shell, cluster hole

Article number	Description
183-201/42	O-Ø 42 mm, I-Ø 36 mm, for Insert Size A
183-201/44	O-Ø 44 mm, I-Ø 36 mm, for Insert Size A
183-201/46	O-Ø 46 mm, I-Ø 40 mm, for Insert Size B
183-201/48	O-Ø 48 mm, I-Ø 40 mm, for Insert Size B
183-201/50	O-Ø 50 mm, I-Ø 44 mm, for Insert Size C
183-201/52	O-Ø 52 mm, I-Ø 44 mm, for Insert Size C
183-201/54	O-Ø 54 mm, I-Ø 48 mm, for Insert Size D
183-201/56	O-Ø 56 mm, I-Ø 48 mm, for Insert Size D
183-201/58	O-Ø 58 mm, I-Ø 52 mm, for Insert Size E
183-201/60	O-Ø 60 mm, I-Ø 52 mm, for Insert Size E
183-201/62	O-Ø 62 mm, I-Ø 54 mm, for Insert Size F
183-201/64	O-Ø 64 mm, I-Ø 54 mm, for Insert Size F
183-201/66	O-Ø 66 mm, I-Ø 54 mm, for Insert Size F
183-201/68	O-Ø 68 mm, I-Ø 54 mm, for Insert Size F
183-201/70	O-Ø 70 mm, I-Ø 54 mm, for Insert Size F
183-201/72	O-Ø 72 mm, I-Ø 54 mm, for Insert Size F

PlasmaLink Shell, multi hole

Article number	Description
183-310/50	O-Ø 50 mm, I-Ø 44 mm, for Insert Size C
183-310/52	O-Ø 52 mm, I-Ø 44 mm, for Insert Size C
183-310/54	O-Ø 54 mm, I-Ø 48 mm, for Insert Size D
183-310/56	O-Ø 56 mm, I-Ø 48 mm, for Insert Size D
183-310/58	O-Ø 58 mm, I-Ø 52 mm, for Insert Size E

183-310/60	O-Ø 60 mm, I-Ø 52 mm, for Insert Size E
183-310/62	O-Ø 62 mm, I-Ø 54 mm, for Insert Size F
183-310/64	O-Ø 64 mm, I-Ø 54 mm, for Insert Size F
183-310/66	O-Ø 66 mm, I-Ø 54 mm, for Insert Size F
183-310/68	O-Ø 68 mm, I-Ø 54 mm, for Insert Size F
183-310/70	O-Ø 70 mm, I-Ø 54 mm, for Insert Size F
183-310/72	O-Ø 72 mm, I-Ø 54 mm, for Insert Size F
183-310/74	O-Ø 74 mm, I-Ø 66 mm, for Insert Size G
183-310/76	O-Ø 76 mm, I-Ø 66 mm, for Insert Size G
183-310/78	O-Ø 78 mm, I-Ø 66 mm, for Insert Size G
183-310/80	O-Ø 80 mm, I-Ø 66 mm, for Insert Size G

TiCaP Shell, multi hole

Article number	Description
183-301/50	O-Ø 50 mm, I-Ø 44 mm, for Insert Size C
183-301/52	O-Ø 52 mm, I-Ø 44 mm, for Insert Size C
183-301/54	O-Ø 54 mm, I-Ø 48 mm, for Insert Size D
183-301/56	O-Ø 56 mm, I-Ø 48 mm, for Insert Size D
183-301/58	O-Ø 58 mm, I-Ø 52 mm, for Insert Size E
183-301/60	O-Ø 60 mm, I-Ø 52 mm, for Insert Size E
183-301/62	O-Ø 62 mm, I-Ø 54 mm, for Insert Size F
183-301/64	O-Ø 64 mm, I-Ø 54 mm, for Insert Size F
183-301/66	O-Ø 66 mm, I-Ø 54 mm, for Insert Size F
183-301/68	O-Ø 68 mm, I-Ø 54 mm, for Insert Size F
183-301/70	O-Ø 70 mm, I-Ø 54 mm, for Insert Size F
183-301/72	O-Ø 72 mm, I-Ø 54 mm, for Insert Size F
183-301/74	O-Ø 74 mm, I-Ø 66 mm, for Insert Size G
183-301/76	O-Ø 76 mm, I-Ø 66 mm, for Insert Size G
183-301/78	O-Ø 78 mm, I-Ø 66 mm, for Insert Size G
183-301/80	O-Ø 80 mm, I-Ø 66 mm, for Insert Size G

TrabecuLink Shell, multi hole

Article number	Description
183-401/50	O-Ø 50 mm, I-Ø 44 mm, for Insert Size C
183-401/52	O-Ø 52 mm, I-Ø 44 mm, for Insert Size C
183-401/54	O-Ø 54 mm, I-Ø 48 mm, for Insert Size D
183-401/56	O-Ø 56 mm, I-Ø 48 mm, for Insert Size D
183-401/58	O-Ø 58 mm, I-Ø 52 mm, for Insert Size E
183-401/60	O-Ø 60 mm, I-Ø 52 mm, for Insert Size E
183-401/62	O-Ø 62 mm, I-Ø 54 mm, for Insert Size F
183-401/64	O-Ø 64 mm, I-Ø 54 mm, for Insert Size F
183-401/66	O-Ø 66 mm, I-Ø 54 mm, for Insert Size F
183-401/68	O-Ø 68 mm, I-Ø 54 mm, for Insert Size F
183-401/70	O-Ø 70 mm, I-Ø 54 mm, for Insert Size F
183-401/72	O-Ø 72 mm, I-Ø 54 mm, for Insert Size F
183-401/74	O-Ø 74 mm, I-Ø 66 mm, for Insert Size G
183-401/76	O-Ø 76 mm, I-Ø 66 mm, for Insert Size G
183-401/78	O-Ø 78 mm, I-Ø 66 mm, for Insert Size G
183-401/80	O-Ø 80 mm, I-Ø 66 mm, for Insert Size G

Ceramic Inserts Biolox[®] Delta

Article number	Description
183-520/28	Size A (O-Ø 36 mm) / for Head-Ø 28 mm
183-530/28	Size B (O-Ø 40 mm) / for Head-Ø 28 mm
183-530/32	Size B (O-Ø 40 mm) / for Head-Ø 32 mm
183-540/32	Size C (O-Ø 44 mm) / for Head-Ø 32 mm
183-540/36	Size C (O-Ø 44 mm) / for Head-Ø 36 mm
183-550/32	Size D (O-Ø 48 mm) / for Head-Ø 32 mm
183-550/36	Size D (O-Ø 48 mm) / for Head-Ø 36 mm
183-550/40	Size D (O-Ø 48 mm) / for Head-Ø 40 mm
183-560/32	Size E (O-Ø 52 mm) / for Head-Ø 32 mm
183-560/36	Size E (O-Ø 52 mm) / for Head-Ø 36 mm
183-560/40	Size E (O-Ø 52 mm) / for Head-Ø 40 mm
183-570/36	Size F (O-Ø 54 mm) / for Head-Ø 36 mm
183-570/40	Size F (O-Ø 54 mm) / for Head-Ø 40 mm

Ceramic Inserts LINK CeraDur

Article number	Description
183-521/28	Size A (O-Ø 36 mm) / for Head-Ø 28 mm
183-531/28	Size B (O-Ø 40 mm) / for Head-Ø 28 mm
183-531/32	Size B (O-Ø 40 mm) / for Head-Ø 32 mm
183-541/32	Size C (O-Ø 44 mm) / for Head-Ø 32 mm
183-541/36	Size C (O-Ø 44 mm) / for Head-Ø 36 mm
183-551/32	Size D (O-Ø 48 mm) / for Head-Ø 32 mm
183-551/36	Size D (O-Ø 48 mm) / for Head-Ø 36 mm
183-551/40	Size D (O-Ø 48 mm) / for Head-Ø 40 mm
183-561/32	Size E (O-Ø 52 mm) / for Head-Ø 32 mm
183-561/36	Size E (O-Ø 52 mm) / for Head-Ø 36 mm
183-561/40	Size E (O-Ø 52 mm) / for Head-Ø 40 mm
183-571/36	Size F (O-Ø 54 mm) / for Head-Ø 36 mm
183-571/40	Size F (O-Ø 54 mm) / for Head-Ø 40 mm

X-LINKed® Insert

Article number	Description
Neutral	
183-350/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-351/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-351/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-352/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-352/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-352/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-353/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-353/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-353/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-354/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-354/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-354/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-355/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-355/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm

183-355/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-356/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-356/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-356/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
Shoulder height 5 mm	
183-740/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-741/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-741/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-742/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-742/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-742/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-743/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-743/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-743/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-744/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-744/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-744/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-745/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-745/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-745/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-746/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-746/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-746/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 4 mm offset	
183-750/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-751/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-751/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-752/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-752/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-752/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-753/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-753/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-753/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-754/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-754/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm

183-754/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-755/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-755/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-755/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-756/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-756/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-756/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 4 mm offset with shoulder	
183-760/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-761/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-761/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-762/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-762/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-762/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-763/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-763/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-763/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-764/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-764/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-764/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-765/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-765/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-765/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-766/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-766/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-766/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 4 mm offset, 10° inclination	
183-770/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-771/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-771/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-772/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-772/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-772/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-773/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-773/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm

183-773/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-774/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-774/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-774/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-775/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-775/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-775/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-776/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-776/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-776/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 8 mm offset, 20° inclination	
183-780/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-781/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-781/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-782/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-782/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-782/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-783/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-783/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-783/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-784/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-784/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-784/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-785/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-785/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-785/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
+ 12 mm offset, 20° inclination	
183-786/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-786/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-786/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm

E-Dur® Inserts (X-LINKed Vit E PE)

Article number	Description
Neutral	
183-360/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-361/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-361/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-362/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-362/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-362/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-363/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-363/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-363/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-364/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-364/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-364/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-365/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-365/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-365/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-366/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-366/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-366/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
Shoulder height 5 mm	
183-370/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-371/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-371/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-372/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-372/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-372/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-373/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-373/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-373/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-374/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-374/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-374/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm

183-375/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-375/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-375/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-376/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-376/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-376/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 4 mm offset	
183-850/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-851/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-851/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-852/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-852/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-852/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-853/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-853/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-853/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-854/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-854/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-854/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-855/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-855/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-855/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-856/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-856/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-856/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 4 mm offset with shoulder	
183-860/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-861/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-861/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-862/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-862/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-862/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-863/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-863/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-863/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm

183-864/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-864/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-864/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-865/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-865/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-865/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-866/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-866/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-866/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 4 mm offset, 10° inclination	
183-870/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-871/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-871/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-872/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-872/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-872/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm
183-873/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-873/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-873/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-874/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-874/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-874/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-875/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-875/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-875/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
183-876/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-876/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-876/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm
+ 8 mm offset, 20° inclination	
183-880/28	Size A (A-Ø 36 mm) / for Head-Ø 28 mm
183-881/28	Size B (A-Ø 40 mm) / for Head-Ø 28 mm
183-881/32	Size B (A-Ø 40 mm) / for Head-Ø 32 mm
183-882/28	Size C (A-Ø 44 mm) / for Head-Ø 28 mm
183-882/32	Size C (A-Ø 44 mm) / for Head-Ø 32 mm
183-882/36	Size C (A-Ø 44 mm) / for Head-Ø 36 mm

183-883/28	Size D (A-Ø 48 mm) / for Head-Ø 28 mm
183-883/32	Size D (A-Ø 48 mm) / for Head-Ø 32 mm
183-883/36	Size D (A-Ø 48 mm) / for Head-Ø 36 mm
183-884/28	Size E (A-Ø 52 mm) / for Head-Ø 28 mm
183-884/32	Size E (A-Ø 52 mm) / for Head-Ø 32 mm
183-884/36	Size E (A-Ø 52 mm) / for Head-Ø 36 mm
183-885/28	Size F (A-Ø 54 mm) / for Head-Ø 28 mm
183-885/32	Size F (A-Ø 54 mm) / for Head-Ø 32 mm
183-885/36	Size F (A-Ø 54 mm) / for Head-Ø 36 mm
+ 12 mm offset, 20° inclination	
183-886/28	Size G (A-Ø 66 mm) / for Head-Ø 28 mm
183-886/32	Size G (A-Ø 66 mm) / for Head-Ø 32 mm
183-886/36	Size G (A-Ø 66 mm) / for Head-Ø 36 mm

Dual Mobility Insert

Article number	Description
183-905/01	Size B, for Metal Shell 46-48, for Liner 44/22
183-910/01	Size C, for Metal Shell 50-52, for Liner 48/28
183-915/01	Size D, for Metal Shell 54-56, for Liner 52/28
183-920/01	Size E, for Metal Shell 58-60, for Liner 56/28
183-925/01	Size F, for Metal Shell 62-72, for Liner 58/28
183-930/01	Size G, for Metal Shell 74-80, for Liner 70/28

Shell/Insert Adapter

Article number	Description
Neutral	
183-580/01	O-Ø 44 mm, I-Ø 40 mm, for Metal Shell 50-52 mm, for Insert Size B
183-580/02	O-Ø 48 mm, I-Ø 44 mm, for Metal Shell 54-56 mm, for Insert Size C
183-580/03	O-Ø 52 mm, I-Ø 48 mm, for Metal Shell 58-60 mm, for Insert Size D
183-580/04	O-Ø 54 mm, I-Ø 48 mm, for Metal Shell 62-72 mm, for Insert Size D
183-580/05	O-Ø 66 mm, I-Ø 54 mm, for Metal Shell 74-80 mm, for Insert Size F
+ 4 mm offset	
183-590/01	O-Ø 40 mm, I-Ø 36 mm, for Metal Shell 46-48 mm, for Insert Size A
183-590/02	O-Ø 44 mm, I-Ø 40 mm, for Metal Shell 50-52 mm, for Insert Size B
183-590/03	O-Ø 48 mm, I-Ø 44 mm, for Metal Shell 54-56 mm, for Insert Size C
183-590/04	O-Ø 52 mm, I-Ø 48 mm, for Metal Shell 58-60 mm, for Insert Size D
183-590/05	O-Ø 54 mm, I-Ø 48 mm, for Metal Shell 62-72 mm, for Insert Size D
183-590/06	O-Ø 66 mm, I-Ø 54 mm, for Metal Shell 74-80 mm, for Insert Size F
+ 4 mm offset, 10° inclination	
183-600/01	O-Ø 44 mm, I-Ø 40 mm, for Metal Shell 50-52 mm, for Insert Size B
183-600/02	O-Ø 48 mm, I-Ø 44 mm, for Metal Shell 54-56 mm, for Insert Size C
183-600/03	O-Ø 52 mm, I-Ø 48 mm, for Metal Shell 58-60 mm, for Insert Size D
183-600/04	O-Ø 54 mm, I-Ø 48 mm, for Metal Shell 62-72 mm, for Insert Size D
183-600/05	O-Ø 66 mm, I-Ø 54 mm, for Metal Shell 74-80 mm, for Insert Size F
183-600/06	O-Ø 40 mm, I-Ø 36 mm, for Metal Shell 46-48 mm, for Insert Size A
+ 8 mm offset, 20° inclination	
183-610/01	O-Ø 44 mm, I-Ø 40 mm, for Metal Shell 50-52 mm, for Insert Size B
183-610/02	O-Ø 48 mm, I-Ø 44 mm, for Metal Shell 54-56 mm, for Insert Size C
183-610/03	O-Ø 52 mm, I-Ø 48 mm, for Metal Shell 58-60 mm, for Insert Size D
183-610/04	O-Ø 54 mm, I-Ø 48 mm, for Metal Shell 62-72 mm, for Insert Size D
183-610/06	O-Ø 40 mm, I-Ø 36 mm, for Metal Shell 46-48 mm, for Insert Size A
+ 12 mm offset, 20° inclination	
183-610/05	O-Ø 66 mm, I-Ø 54 mm, for Metal Shell 74-80 mm, for Insert Size F

Screws

Article number	Description
183-700/00	Pole Screw, spare part
183-710/00	Adapter fixation screw, spare part