

## WHAT IS HBM

H HONEST
B BETTER
M MUTUAL

In HBM-We respect the HONESTY, do BETTER, and share MUTUAL benefits.

# Medispo®

**BEST IN MEDICAL DISPOSABLE** 





#### WE MAKE THE BEST WE CARE THE MOST

www.hbmchina.com

gaochen@hbmchina.com

• 1508-09, No. 211, Golden Port Road, Shanghai, China



# Medispo®

### **Disposable Face Mask**

with ear-loop




BFE **≥ 95**% Type I: Type II: BFE ≥ 98% Type IIR: BFE ≥ 98%

<Bacterial Filtration Efficiency>









Three Layers Design

- Disposable
- Odorless
- 3 layers design
- Comfort and fits perfectly
- Free of fiber glass
- Hypoallergic
- With nose wire support
- Low resistance for better breathing

#### **PACKING INFORMATION**

Packing:	50pc/box, 40box/carton
Net Weight:	7.3kgs/ctn
Gross Weight:	7.9kgs/ctn
Carton Size:	52x40x30cm

#### **INSTRUCTIONS**

- 1. Put on the mask, hang on the loops to right and left ear.
- 2. Using hand to mould the nose piece to the shape of your nose, ensure a close fit and good seal.
- 3. Fit check before using, mask sure no air leaks at the mask edge.









### **DISPOSABLE FACE MASK** 50PCS/BOX

Size:

Length 175mm Width folded 95mm Width unfolded 170mm Length of Earloop 170mm

**Product Code: TYPE I: 966-EL** TYPE II: 966-EL II

TYPE IIR: 966-EL IIR

# **Medispo**<sup>®</sup>

**Anti-Fog** 

# **Disposable Medical** Face Mask Type II with Ties



Type II: BFE ≥ 98%

<Bacterial Filtration Efficiency>











#### Fluid Resistance

Tests penetration resistance to synthetic blood at three protection levels—120 mm Hg.



#### **Bacterial Filtration Efficiency (BFE)**

Tests filtration ability against an aerosol containing bacteria 3.0 microns in size.



# **Differential Pressure (△P)**

Gauges air flow from one side of a mask to the other, assessing breathability.

- · Made of non-paper, non-woven material
- Odorless
- Hypoallergic
- Head straps, of two layers with the same size for perfect fitting on the face
- Ultrasonic Bonding of the mask with the head straps
- · Tear resistant.
- Plastic/Wire Nose clip 12cm, for perfect and stable application of the mask on the nose
- Respiratory Resistance Differential Pressure (Delta P ΔP): <60 (Pa / cm<sup>2</sup>).

#### **Dimensions:**

Length 175mm Width folded 95mm Width unfolded 180mm controlled-partially lint free

#### Three Layers Design

#### Layer 1

the colored layer is your first line of defense

#### Laver 2

protects against fluid while maintaining

#### Layer 3

soft.non-abrasive inner layer makes the mask comfortable on your skin

With anti-fog non-woven strip on inner layer which can reduce pressure on the bridge



### **DISPOSABLE MEDICAL FACE MASK** TYPE II WITH TIES

50CS/BOX Product Code: 966-TO-AF

#### **PACKING INFORMATION**

Packing:	50pc/box, 40box/carton
Net Weight:	8.0kgs/ctn
Gross Weight:	9.0kgs/ctn
Carton Size:	52x39x52cm