


X rays film viewers




Aluminum structure!!!

X rays film viewers

- **Frame:** made of aluminum profile pre-painted with epoxy powder (RAL 7035), the components are connected with nylon corner joints
- **Light source:** fluorescent neon tubes from 15W to 58 W
- **Diffuser:** white acrylic sheet
- **Film locking system:** included
- **Power Supply:** 230V; 50/60 Hz

- **Switch:** ON/OFF bipolar switch with a plug with fuse holder
- **Electrical wiring:** self-extinguishing PVC lugs
- **Components:** compliant to CEI regulations and IMQ, UL and DVE approvals

- **Compliance:** the device is in conformity with the essential requirements of the MDR745/2017 Regulatory and further modifications and integrations as Class I medical device

Models	Cod.	Switch #	Visual area (cm)	Overall dimensions (cm)			Weight Kg	Color Temperature °K	Brightness flux (lm)	Chromatic Index	Total Power (Watt)
				Width	Height	Thickness					
 1 Panel	BF AL 43.43 OR	1	38x38	43	43	12	6	6500	2x700	63	2x15
 1 Panels	BF AL 43.43D	1	38x38	43	43	12	6	6500	2x700	63	2x15
 1,5 Panels	BF AL 43.70 OR	1	38x62	67	43	12	8	6500	2x1100	63	2x18
 2 Panels	BF AL 43.90 OR	1	38x92	97	43	12	11	6500	2x1700	63	2x30
 3 Panels	BF AL 43.120 OR	1	38x122	127	43	12	14	6500	2x2850	63	2x36
 4 Panels	BF AL 43.150 OR	1	38x153	158	43	12	18	6500	2x4600	63	2x58
 2x3 Panels	BF AL 86.120B	2	76x122	127	2x43	12	28	6500	4x2850	63	4x36
 2x4 Panels	BF AL 86.150B	2	76x153	158	2x43	12	36	6500	4x4600	63	4x58
 1,5 Panels	BF AL 43.70 VE	1	62x38	43	67	12	8	6500	2x1100	63	2x18
 2 Panels	BF AL 43.90 VE	1	92x38	43	97	12	11	6500	2x1700	63	2x30
 3 Panels	BF AL 43.120 VE	1	122x38	43	127	12	14	6500	2x2850	63	2x36
 4 Panels	BF AL 43.150 VE	1	153x38	43	158	12	18	6500	2x4600	63	2x58



weiko
health base

WEIKO - BIEFFE ITALIA s.r.l.

Legal Address:
Viale Lincoln, 178
81100 Caserta
info@weiko.com
www.weiko.com

Factory address:
Consorzio Sinè
Zona ASI Aversa Nord
81032 Carinaro (CE)
Ph. +39 081 8654662
Fax +39 081 8654723

www.weiko.com