

C-mount camera – HDMI KERN ODC-85



**Features**

- The ODC 851 HDMI microscope camera has been specially developed for direct HDMI connection to your HDMI compatible display device. The images can be stored straight onto the SD card which is delivered with the product or can be transferred to your PC or laptop for further processing using the USB 2.0 cable in combination with the OXM 901 software.
- The HDMI autofocus camera ODC 852 offers you a perfect, effective solution for modern microscopy. The autofocus function automatically detects and adjusts the focus level so that you always have a razor-sharp image. Ideal for all applications in connection with a KERN stereo microscope.
- Realtime images can be transferred to an HDMI-compatible display device using the HDMI connection and they can also be stored on the SD card which was delivered with the product. As an alternative, data can also be transferred using the WLAN module (ODC 852) to a PC or laptop in combination with the KERN OXM 902 software which is included with the delivery
- Power supply is from an external 12 V power unit
- Scope of delivery ODC 851: Camera, USB mouse, USB 2.0 cable (length: 2 m), HDMI cable (length: 2 m), SD card (16 GB) and camera software Microscope VIS Basic KERN OXM 901
- Scope of delivery ODC 852: Camera, USB mouse, HDMI cable (length: 2 m), SD card (16 GB), WiFi adapter and camera software Microscope VIS Pro KERN OXM 902
- Please order the appropriate C-mount adapter to fit your KERN microscope now

STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system
<b>KERN</b>							
<b>ODC 851</b>	2 MP	HDMI, USB 2.0, SD	30 – 60	CMOS	1/2,8"	colour	Win XP, Vista, 7, 8, 10
<b>ODC 852*</b>	5 MP	HDMI, USB 2.0, SD, WLAN	25 – 60	CMOS	1/1,8"	colour	Win XP, Vista, 7, 8, 10

\*can only be used in combination with stereo microscopes

C-mount camera – High resolution KERN ODC-86

The cooled camera for professional fluorescence examinations



**Features**

- The ODC 861 camera with Peltier cooling technology has been specially designed for fluorescent applications. It is able to significantly compensate for image noise associated with weak lighting. Due to its high resolution and light-sensitive Sony CMOS colour sensor it proves first-class images. The practical, sturdy storage box serves as protection and for transportation of this premium camera
- Realtime images can be transferred straight to a PC or laptop using the integrated USB 3.0 interface. As an alternative, 2 USB 2.0 interfaces are available, to operate the camera with the KERN OXM 902 software which is included with the delivery
- Power supply is from an external 12 V power unit
- Please order the appropriate C-mount adapter (only 1,0× possible) to fit your KERN microscope now

STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system
<b>KERN</b>							
<b>ODC 861</b>	20 MP	USB 3.0	5 – 30	CMOS	1"	colour	Win XP, Vista, 7, 8, 10

Can only be used in combination with compound microscopes

## Pictograms

<b>360° rotatable microscope head</b>	<b>Fluorescence illumination for compound microscopes</b> With 3 W LED illumination and filter	<b>USB 3.0 digital camera</b> For direct transmitting of the picture to a PC
<b>Monocular Microscope</b> For the inspection with one eye	<b>Phase contrast unit</b> For a higher contrast	<b>WLAN data interface</b> For transmitting of the picture to a mobile display device
<b>Binocular Microscope</b> For the inspection with both eyes	<b>Darkfield condenser/unit</b> For a higher contrast due to indirect illumination	<b>HDMI digital camera</b> For direct transmitting of the picture to a display device
<b>Trinocular Microscope</b> For the inspection with both eyes and the additional option for the connection of a camera	<b>Polarising unit</b> To polarise the light	<b>PC software</b> To transfer the measurements from the device to a PC
<b>Abbe Condenser</b> With high numerical aperture for the concentration and the focusing of light	<b>Infinity system</b> Infinity corrected optical system	<b>Automatic temperature compensation</b> For measurements between 10 °C and 30 °C
<b>Halogen illumination</b> For pictures bright and rich in contrast	<b>Zoom magnification</b> For stereomicroscopes	<b>Protection against dust and water splashes IPxx:</b> The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013
<b>LED illumination</b> Cold, energy-saving and especially long-life illumination	<b>Auto-focus</b> For automatic control of the focus level	<b>Battery operation</b> Ready for battery operation. The battery type is specified for each device.
<b>Incident illumination</b> For non-transparent objects	<b>Parallel optical system</b> For stereomicroscopes, enables fatigue-proof working	<b>Battery operation rechargeable</b> Prepared for a rechargeable battery operation
<b>Transmitting illumination</b> For transparent objects	<b>Integrated scale</b> In the eyepiece	<b>Plug-in power supply</b> 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
<b>Fluorescence illumination</b> For stereomicroscopes	<b>SD card</b> For data storage	<b>Integrated power supply unit</b> Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
<b>Fluorescence illumination for compound microscopes</b> With 100 W mercury lamp and filter	<b>USB 2.0 digital camera</b> For direct transmitting of the picture to a PC	<b>Package shipment</b> The time required to manufacture the product internally is shown in days in the pictogram.

## Abbreviations

<b>C-Mount</b> Adapter for the connection of a camera to a trinocular microscope	<b>LWD</b> Long Working Distance	<b>SWF</b> Super Wide Field (Field number at least $\varnothing$ 23 mm for 10 $\times$ eyepiece)
<b>FPS</b> Frames per second	<b>N.A.</b> Numerical Aperture	<b>W.D.</b> Working Distance
<b>H(S)WF</b> High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	<b>SLR camera</b> Single-Lens Reflex camera	<b>WF</b> Wide Field (Field number up to $\varnothing$ 22 mm for 10 $\times$ eyepiece)

Your KERN specialist dealer: