## Certificate of Compliance

ECM Parred

No. 3O190517.SLXDT22

Technical Construction File no. CE-2019-A0

Certificate's Shanghai Lu Xiangyi Centrifuge Instrument

Holder: Co., Ltd.

No.9, Lane 4390, Hunan Rd, Shanghai, 201318 China

Certification ECM Mark:

Model(s):



Product: High-Speed Centrifuge, Large capacity

refrigerated Centrifuge, Gel Card Incubator,

Low-Speed Refrigerated Centrifuge, High-Speed Refrigerated Centrifuge, Low Speed Centrifuge

(see the following annex I)

Verification to: Standard:

EN ISO 14971:2012, EN ISO 15223-1:2016,

EN 1041:2013

related to CE Directive(s): 2014/35/EU (Low Voltage)

2014/30/EU (Electromagnetic Compatibility)

**Remark:** The product(s) has been verified on a voluntary basis. The product(s) satisfies the requirements of the Certification Mark of ECM, in reference to the above listed Standard(s). The above Compliance Mark can be affixed on the product(s) accordingly to the ECM regulation about its release and its use. The regulation can be found at www.entecerma.it. This Certificate of Compliance can be checked for validity at www.entecerma.it

This verification doesn't imply assessment of the production of the product(s).

Additional information, clarification about the  $\mathbf{C}\mathbf{E}$  Marking:



We attest that a TCF for the CE Marking process is in place. Whereas the Manufacturer is Responsible to start the CE Marking Certification Procedure and to perform all the necessary activities, as required by the Directive before placing the CE Mark on the product(s).

Date of issue 17 May 2019

Chief Manager
Morad Morina

Expiry date 16 May 2024

Deputy Manager Amanda Payne

## Annex I

No. 3O190517.SLXDT22

Technical Construction File no. CE-2019-A0



Product	Model
High-Speed Centrifuge	TG20.5, TG19, TG18.5, TG16.5, TG16, TG16A,
	TG12X, TD10K
Large capacity refrigerated Centrifuge	L800R, DL-8M, L600R, DL-6M, DL-5M
Gel card incubator	F37-12X2
Low-Speed Refrigerated Centrifuge	TDL-5M, TDL-8M, L580R, DL-5B, DL-5T, TDL-5T, DL-5T, TDL-4T
High-Speed Refrigerated Centrifuge	TGL-25M, TGL-16M, TGL-16.5M, TGL-17M, TGL-18M, TGL-20M, TGL-21M, H1200R, GL-20.5M, H2100R, H2200R, H2500R, GL-25M, GL-22M, GL-21M, GL-12M, GL-23M, CSC-12S, CSC-11S, CSC-10S, H1400pF
Low Speed Centrifuge	TD6, L580, TD5.5, TD5M, TD5A, TD5, TD6B, TD5B, TD4B, TD4, TD4A, TD5P, TD4P, TD5G, TD5Z, TD4X, TD4G, TD3, TD4Y, TD5GL, TD5X, TD4N, TD6K, TD4K, L420-RZ, D5M, D5B, D5T, TD4T, TD5T, LDJ-5MD, LDJ-5M