



# D19C Densitometer

Ready To Meet Your Needs Today,  
Equipped For Tomorrow's Requirements



**gretagmacbeth**  
YOUR COLOR. PRECISELY.



GretagMacbeth ColorNet™

# D19C

## Specifications

Basic model functions are already checked. Choose the additional functions you would like and put together your made-to-measure densitometer.

### Measuring functions

- Density
- All densities, gray balance
- Density difference
- All Density differences
- Dot gain
- Impression line
- Dot area
- Printing plate measurement
- Contrast
- Trapping
- Hue error / Grayness
- Auto Function 1 / Auto Function 2
- User password protection
- Automatic color detection
- Polarization filters
- Without Polarization filters
- Normed filters for all standard colors and black
- Display reversal
- Display contrast adjustable
- Interface for printer / computer
- Measurement data with date and time printable
- Extendable measuring head
- Step-by-step user guidance with the control wheel
- 32 reference values stored
- Ring lens system
- Data interface RS 232 C

### Operation

Control wheel and measuring key

### Display

Digital LCD, 160 x 128 pixels, full graphics

### Measuring geometry

0°/45° Ring lens system

### Light source

Filament bulb approx. 2856 K

### Color filter:

Filter set 47B DIN 16536

Filter set 47 ANSI status T

Filter set NB DIN 16536 interference filter

Filter set SPI ISO status I interference filter

### Measuring range

0.00 D – 2.50 D

### Reproducibility

± 0.01 D

± 1 % (for dot area)

### Linearity

± 0.01 D or ± 1 %

### Interinstrument agreement

± 0.02 D or ± 2 %

### Measuring aperture

Ø 3.6 mm (9/64 in)

### Calibration

Slope: For density measurement

Zero: Automatic

### Polarization filter

2x linear (tube P)

### Warm-up time

none

### Power supply

Rechargeable battery NiMH, nom. 7.2 V, 1000 mAh, Rechargeable battery NiCd, nom. 7.2 V, 600 mAh

### Charge time

approx. 3 hours, automatic disconnection

### Charge status

automatic capacity checking and display; additional lithium battery for data memory

### Measurements per charge

approx. 6'000

(with rechargeable battery NiMH)

### Measuring time

approx. 0.8 s

### Data interface

RS 232 C. Densitometer can be controlled by a remote computer (details available on request)

### Clock

Date and exact time

### Weight

approx. 890 g (1.96 lb)

### Dimensions

8.3 x 8.0 x 24.5 cm (3.3 x 3.2 x 9.6 in)

### Accessories

Calibration card, operating manual, charger

Specifications subject to change without notice

For more information on the D19C, please contact your nearest GretagMacbeth representative.

**gretagmacbeth**  
YOUR COLOR. PRECISELY.

Switzerland: Althardstrasse 70, CH-8105 Regensdorf, Tel: +41 1 842 24 00, Fax: +41 1 842 22 22  
United States: 617 Little Britain Road, New Windsor, NY 12553-6148, Tel: 800-622-2384, 914-565-7660 (Outside USA and Canada), Fax: 914-561-0267  
Germany: Siemensstrasse 11, D-63263 Neu-Isenburg, Tel: +49 61 02 79 57 0, Fax: +49 61 02 79 57 57  
United Kingdom: Macbeth House, Pacific Road, Altrincham, Cheshire WA145BJ, Tel: +44 161 926 9822, Fax: +44 161 926 9835  
China: 12A Wardley Centre, 9-11 Prat Avenue, Tsimshatsui, Kowloon, Hong Kong, Tel: +852 2368 7738, Fax: +852 2368 6717

Visit our World Wide Web Site at [www.gretagmacbeth.com](http://www.gretagmacbeth.com)

™ Trademark of GretagMacbeth. GretagMacbeth is an ISO 9001 certified company.

Part No. 98.26.56 en (5/98)  
Printed in Switzerland